

Laredo LMC

Medium-size Wallpacks

LED WALLPACKS



*3000K and warmer CCTs only

Laredo 30 LED medium size wallpack offers both wide spacing and excellent uniformity. The 30 LED unit is available in lumen packages ideal for mounting heights from 12 to 18 feet, providing spacings of up to five times the mounting height. The 30 LED unit is available in a Type II, III or IV forward throw distributions.

- Die-cast aluminum with a hinged back-plate for ease of installation and maintenance
- The LED bezel and trim-plate are made of stainless steel
- Listed to UL1598 for use in wet locations
- 0-10V dimming driver standard
- Quick-mount adapter that allows installation without opening the fixture.

- 20KA surge protection with an end of life LED indicator
- Zero uplight (U0), dark sky, neighbor friendly optics
- DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org

Battery Backup:

Designed to meet strict 1fc minimum requirements. At 12ft mounting height 1fc covers 16x16ft area, well beyond the 10x10ft standard; No uplight, external test button; 120V or 277V only; Rated -20° C to 35° C

MADE-TO-ORDER ORDERING INFORMATION



SERIES	NUMBER OF LEDS/SOURCE/VOLTAGE	CCT	IES DISTRIBUTION	DRIVE CURRENT	FINISH	OPTIONS
LMC Laredo Medium	30LU 30 LEDs, Universal voltage 120-277V 30L1 30 LEDs, 120V 30L2 30 LEDs, 208V 30L3 30 LEDs, 240V 30L4 30 LEDs, 277V 30LF 30 LEDs, 347V 30L5 30 LEDs, 480V	3K 3000K nominal, 80 CRI 4K 4000K nominal, 70 CRI 5K 5000K nominal, 67 CRI	2 Type II 3 Type III 4 Type IV (Forward throw)	BLANK Std. is 700mA 035 350mA	1 Bronze 2 Black 3 Gray 4 White 5 Platinum	BBU¹ Integral battery for 120 or 277V, rated for -20° C ambient; Available in 350mA (035) drive current only PC¹ Button photocontrol (must specify voltage per footnote 1, not available in 480V) F¹ Fusing (specify voltage per footnote) SCP^{1,2,3} Programmable motion control, factory default is 10% light output

1 Specify voltage, for PC(X) and F(X), replace X with 1-120V, 2-208V, 3-240V, 4-277V, 6-347V, 5-480V
 2 Must order minimum of one SCP-REMOTE to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings, 120V-277V only
 3 PC option not applicable, included in sensor

SPECIFY SCP HEIGHT

- 8F** Up to 8ft mount height
- 20F** Up to 20ft mount height

PERFORMANCE INFORMATION

Series Number	Equivalency		Energy Savings	Delivered Lumens	System Watts	Lumens Per Watt	Mounting Height	CCT	Voltage	Drivers/Current
	MH	HPS								
LMC-30L-035	150w	150w	81%	4,000	35	113	10-15 ft.	5000K	120-277V	1@350mA
LMC-30L	250w	250w	76%	7,300	70	105	12-18 ft.	5000K	120-277V	2@700mA

ACCESSORIES/REPLACEMENT PARTS - Order Separately


Catalog Number	Description
LMC-SPC	Polycarbonate shield
PBT-1	120V button photocontrol
PBT-234	208/240/277V button photocontrol
93044764	40w, 700mA, 120-277V, 0-10V dimming driver
93052458	20KA surge protection with an end of life LED indicator
SCP-REMOTE	Remote control for SCP option; order at least one per project to program and control



LMC-30LU BBU

1,546 lumens at 14.6w for 5K CCT in battery mode

DIMENSIONS



A	B	C
16"	12.125"	9.0"
406 mm	308 mm	229 mm