

# NRG<sup>®</sup> 300 Series

## Perimeter LED Wallpack



Full polycarbonate front provides vandal resistance and uniform light distribution; Internally painted bronze finish for lasting appearance

- 56 mid power LEDs unit provide long-life with up to 78% energy savings, a perfect upgrade for older units
- Available in 4000K and 5000K CCT models
- Rugged cast aluminum back housing for rigid mounting; Bottom 1/2" conduit knockout for surface conduit wiring

- Units available with or without 120V-277V button photocontrol, see ordering information
- Listed to UL 1598 for use in wet locations
- Tamper resistant center pin Torx hardware included
- DesignLights Consortium (DLC) qualified Consult DLC website for more details: <http://www.designlights.org/QPL>



### STOCK ORDERING INFORMATION

Catalog Number	System Watts	Delivered Lumens	Voltage	CCT	Mounting Height	# Drivers/Current	Weight lbs. (kg)	PKG. CODE
NRG-356L-4K-U	17w	1858	120-277V	4000K	Up to 10 ft.	1@100mA	6 (2.7)	FCC
NRG-356L-4K-U-PC				5000K				
NRG-356L-5K-U		1794						
NRG-356L-5K-U-PC								

### PERFORMANCE INFORMATION

Series Number	Equivalency			Energy Savings
	MH	HPS	CFL	
NRG-356LU	50w	50w	42w	78%


### STOCK ACCESSORIES - Order Separately

Catalog Number	Description	PKG. CODE
PBT-1	Button photocontrol, 120V	SCC
PBT-234	Button photocontrol, 208, 240, 277V	SCC

### MADE-TO-ORDER REPLACEMENT PART

Catalog Number	Description	PKG. CODE
SM352-COVER	Polycarbonate front cover, Bronze	BC

### DIMENSIONS



A	B	C
5.4"	11.0"	6.9"
137 mm	280 mm	175 mm