


TRP2/RDI2/QSP2

GeoPak Architectural Wallpacks

LED WALLPACKS

NEW



Medium sized architectural wallpacks in three stylish shapes accentuate building architecture and provide excellent illumination and uniformity

- Die-cast aluminum with upper and lower casting for ease of installation and maintenance
- The LED bezel and trim-plate are made of stainless steel
- IP65, Wet Location Listed to UL924 and UL1598 Standard.
- 0-10V dimming driver standard
- 10kA surge protector
- Universal spider plate for mounting to standard 3 1/2" and 4" square electrical boxes
- Drivers IP66 and RoHS compliant
- Zero uplight (UO), dark sky, neighbor friendly optics (downlight only)

- Optional Sensor and wireless controls
- Optional Dual Drivers and Dual Power Feeds
- Back box accessory available for surface conduit application
- DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org

Battery Backup:

- Optional Battery Backup provides emergency lighting for the required 90 minute path of egress
- Includes a long-life Lithium Iron Phosphate battery and optional battery heater for cold temperature application
- Spectron® self-testing/self-diagnostic electronics are included standard

MADE-TO-ORDER ORDERING INFORMATION

| FAMILY | LEDS - WATTAGE | CCT | VOLTAGE | FINISH | CONTROL OPTIONS | OPTIONS |
|-----------------|--------------------------|---------------------|---------------------------|----------------------------------|---|--|
| TRP2 Trapezoid | 24L-30 24 LEDs, 30 watts | 3K7 3000K, 70CRI | UNV 120-277V | BL Black Textured | PC Button Photocell | SF ³ Single Fuse & Fuse Holder |
| RDI2 Radius | 24L-50 24 LEDs, 50 watts | 4K7 4000K, 70CRI | 120 120V | DB Dark Bronze Textured Graphite | SCP ^{4,5} Occupancy Sensor Programmable (Dim) | DF ³ Double Fuse & Fuse Holder |
| QSP2 Qtr-Sphere | 24L-70 24 LEDs, 70 watts | 5K7 5000K, 70CRI | 208 208V | GT Textured Gray Textured Matte | SCO ⁴ Occupancy Sensor (On/Off) | E ³ Battery Pack (0°C) |
| | 24L-90 24 LEDs, 90 watts | | 240 240V | GR Light Gray Smooth | SWP ^{3,7} SiteSync Pre-commission | EH ³ Battery Pack (-30°C) with heater |
| | 32L-70 32 LEDs, 70 watts | | 277 277V | GYS Platinum Silver Smooth | SWPM ^{3,4,7,8} SiteSync Pre-commission w/ Occupancy Sensor | 2DR ⁶ Dual Drivers |
| | 32L-90 32 LEDs, 90 watts | | UHV ¹ 347/480V | PS White Textured | | 2PF ⁶ Dual Power Feeds |
| | | | 480 ¹ 480V | WH Custom Color | | CS Comfort Shield |
| | | DISTRIBUTION | | | SPEC SCP/SCO & SWPM MOUNT HEIGHT | |
| | | 1 Type I | | | -8F Up to 8ft mount height | |
| | | 2 Type II | | | -20F Up to 20ft mount height | |
| | | 3 Type III | | | | |
| | | 4 Type IV | | | | |

SECONDARY MOUNTING

- BLANK Downlight Only
- NV² Inverted/Up Mounting

¹ 70 & 90 watt versions only
² Not available with SCP, SCO or SWPM sensor options
³ Must specify voltage (120, 277 or 347V only for SWP & SWP, 120 or 277V only for E & EH)
⁴ PCU option not applicable, included in sensor
⁵ Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings
⁶ Not available with 30w version
⁷ Not available with E/EH options. Must specify group and zone information at time of order. See www.HubbellLighting.com/products/sitesync for future details
⁸ Specify time delay, dimming level and mounting height

ACCESSORIES (ORDER SEPARATELY)

| Catalog Number | Description |
|-------------------------|--|
| SCP-REMOTE ⁷ | Remote control for SCP option. Order at least one per project to program and control dimming settings |
| BB-GEO-XX | Black box with 4 - 1/2" threaded conduit holes, specify finish by replacing "XX" with finish selection, eg. Dark Bronze "DB" |
| SWUSB ^{**} | SiteSync loaded on USB flash drive (Windows based only) |
| SWTAB ^{**} | SiteSync Windows Tablet |
| SWBRG ⁺ | SiteSync Wireless Bridge Node |

* Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings.
^{**} When ordering with SiteSync, one of the following interface options must be chosen an ordered separately. Each option contains the SiteSync License, GUI and Bridge Node.
⁺ If needed, an additional Bridge Node can be ordered.

DIMENSIONS

