

VBBG/VWGG Series

Wet Location Vaportites

WALL/SURFACE



- Wall/ceiling/pendant entry, corridor, tunnel, service area, stairwell, or retro-accent
- 150w maximum medium base incandescent
- Platinum silver protective finish
- VWGG has cast aluminum wall bracket with cast wiring box; Box has external lugs and four side 1/2" hubs for surface conduit and one rear 1/2" access hub
- VBBG has cast aluminum wiring box with external lugs for ceiling mount and four 1/2" hubs for surface conduit;

Wiring box has top 1/2" hub for pendant mount

- All units have water/bug tight gasketing
- All units have medium base porcelain socket
- All units include clear glass protective globe with thread-on cast aluminum guard; Guard includes vandal-resistant set screw
- All units are UL listed for use in wet locations


ORDERING INFORMATION

Catalog Number	Wattage	Mounting	Weight lbs. (kg)
VBBG-150	150	Box/pendant	3 (1.36)
VWGG-150	150	Wall	3.5 (1.59)

REPLACEMENT GLOBES

Catalog Number	Description
VAMG-100	Amber
VBG-100	Blue
VGGP-100	Blue, tempered
VCGP-100	Clear, tempered
VCGPT-100	Clear, tempered w/ Tuffskin® coating
VG-15	Clear, standard, 150w
VG-30	Clear, standard, 300w
VGG-100	Blue Green
VGGP-100	Blue Green, tempered
VPG-100	Purple
VRG-100	Ruby
VRGP-100	Ruby, tempered
VRGP-100	Ruby
VRS-100	Green
VCGP-200	Clear, Tempered
VAMG-200	Amber
VGG-200	Blue Green
VGGP-200	Blue Green, tempered
VBG-200	Blue
VRG-200	Ruby

150w
Lugs: 5" center to center



	A	B	C	D	E	F	G
150w	7"	1 1/2"	9"	7 1/4"	9 3/4"	8 1/2"	4"
	178 mm	38 mm	229 mm	184 mm	248 mm	216 mm	102 mm