

VBGL/VWGL

Wet Location LED Vaportites

- Compact size measuring only 5.2" x 10.4" (wall mount version slightly larger)
- 757 lumens, 11w system, 70 LPW
- Frosted glass lens distributes light evenly without any LED brightness or glare
- Pendant mount version accommodates traditional ½" x 14 NPS threaded conduit
- 120-277V operation, 50/60Hz
- Rugged die-cast aluminum housing with removable cast aluminum guard and vandal resistant set screws included, gray finish
- IP66, listed to UL1598 for use in wet locations (unit is not rated for use in hazardous locations)
- Four color multi-language merchandising carton with application details
- Color globe accessories available: Green, Blue, Yellow and Red



tradeSELECT®

VAPORTITES

STOCK ORDERING INFORMATION

Catalog Number	Construction	Mount	System Wattage	# Drivers/Current	Voltage	Color Temperature	Delivered Lumens	LPW	Weight lbs. (kg)	PKG. CODE
VBGL-1	Globe refractor	Ceiling/Pendant	11	1@250mA	120-277V	4000K	757	70	3.4 (1.54)	FCC
VWGL-1	Globe refractor	Wall	11	1@250mA	120-277V	4000K	757	70	3.6 (1.63)	FCC


STOCK REPLACEMENT GLOBES

Catalog Number	Description	PKG. CODE
VGL-FG	Frosted globe	BC
VGL-GUARD	Guard with set screws	BC
Colored Globes		PKG. CODE
VGL-GN	Green globe	BC
VGL-YW	Yellow globe	BC
VGL-BU	Blue globe	BC
VGL-RD	Red globe	BC

PERFORMANCE INFORMATION

Series Number	Equivalency		Energy Savings
	INC	CFL	
VBGL-1	150w	32w	88%
VWGL-1	150w	32w	88%

DIMENSIONS



	A	B	C
VBGL-1	5.2"	10.4"	-
	132 mm	263 mm	-
VWGL-1	7.3"	11.0"	5.2"
	186 mm	280 mm	132 mm