

EKG LED with PicoPrism®

Shoobox Luminaire LED

SITE / ROADWAY



EKG401 LED

FEATURES

- LED models incorporating patented LED PicoPrism technology
- Classic, shoobox style luminaire for architectural relevance
- Full-cutoff optics



3000K and warmer CCTs only

ORDERING INFORMATION (Example)

1A EKG4011P35 DB 80L5K120 A-25

PSA12-4125A/DB

MOUNTING		EPA
1A	1 Arm Side Mt.	2.1
2B	2 Arm Side Mt.	4.2
2L	2 Arm Side Mt.	3.5
3T	3 Arm Side Mt.	4.5
4C	4 Arm Side Mt.	5.0
1W ³	Single Wall Mt.	—

NOTE: EPA is for Fixture only

FIXTURE FINISH	
BL	Black
DB	Dark Bronze
LG	Light Gray
TT	Titanium
PS	Platinum Silver
WH	White
CC	Custom Color*
DB-A	Dark Bronze Anodized

*Consult representative

FIXTURE OPTIONS	
A-25	Photocell Receptacle
SCL-R	Pole Occupancy Sensor up to 16' ht., Round ⁵
SCL-S	Pole Occupancy Sensor up to 16' ht., Square ⁵
SCH-R	Pole Occupancy Sensor up to 30' ht., Round ⁵
SCH-S	Pole Occupancy Sensor up to 30' ht., Square ⁵


POLE / POLE ARM
See Arms & Poles Selection Guide at www.kimlighting.com for pole EPA & ordering.

FIXTURE		
	EKG401	Current
Type I	EKG4011	P35 = 350mA P70 = 700mA
Type II	EKG4012	
Type III	EKG4013	
Type IV	EKG4014	
Type V	EKG4015	
Type R	EKG401R	
Type L	EKG401L	

ELECTRICAL MODULE ²		
Source	Color Temperature	Voltages
80L 80 LEDs	2K Amber	120 120V
	3K 3000K	208 208V
	4K 4000K	240 240V
	5K 5000K	277 277V
		347 347V ¹
		480 480V ¹

¹ Due to current unavailability of 347V and 480V drivers, specification of these voltages may feature an integral step-down transformer.
² Driver has a 0-10V dimming interface with a dimming range of 10-100%. Compatible with most control systems.
³ Wall attachment must provide adequate fixture support.
⁵ Specify pole diameter if round, voltage and color, e.g. SCL-R4/277/BL.

HID to LED Upgrade Kits available. Contact factory.



side view

front view



arm section

