


HID to LED Upgrade Kit PicoPrism®

WP9S/SAR/STS/SET/LLF

LED UPGRADE KIT



FEATURES

- Reduces energy consumption up to 50% compared to original HID source
- 350mA or 700mA current
- Maintains architectural relevance, application integrity and extends asset value
- 0-10V dimming interface, allowing 0-100% illumination output options
- Full palette of lighting distributions and color temperatures to match existing installations
- Preserves applicable UL/CUL/ETL product listing and manufacturer's warranty
- Compatible driver options for renewable energy systems
- Qualifies for many rebates and tax incentives



ORDERING INFORMATION (Example)

WP9S-LED-KIT3P35

60L5K240

CATALOG NUMBER


WARP9 Small		WARP9 Small		Low Level Flood	
WP9S-LED-KIT1P35	Type I	WP9S-LED-KIT1P70	Type I	LLF10-LED-KITP35	Symmetric, Downward
WP9S-LED-KIT2P35	Type II	WP9S-LED-KIT2P70	Type II	LLF20-LED-KITP35	Assymetric, Right Downward
WP9S-LED-KIT3P35	Type III	WP9S-LED-KIT3P70	Type III	LLF30-LED-KITP35	Assymmetric, Left Downward
WP9S-LED-KIT4P35	Type IV	WP9S-LED-KIT4P70	Type IV	LLF40-LED-KITP35	Symmetric, Upward
WP9S-LED-KIT5P35	Type V	WP9S-LED-KIT5P70	Type V	LLF50-LED-KITP35	Symmetric, Downward, Concealed
WP9S-LED-KITLP35	One Way, Left	WP9S-LED-KITLP70	One Way, Left	LLF60-LED-KITP35	Symmetric, Downward, Concealed w/ Guard
WP9S-LED-KITRP35	One Way, Right	WP9S-LED-KITRP70	One Way, Right		
The Archetype Small		The Archetype Small			
SAR-LED-KIT1P35	Type I	SAR-LED-KIT1P70	Type I		
SAR-LED-KIT2P35	Type II	SAR-LED-KIT2P70	Type II		
SAR-LED-KIT3P35	Type III	SAR-LED-KIT3P70	Type III		
SAR-LED-KIT4P35	Type IV	SAR-LED-KIT4P70	Type IV		
SAR-LED-KIT5P35	Type V	SAR-LED-KIT5P70	Type V		
SAR-LED-KITLP35	One Way, Left	SAR-LED-KITLP70	One Way, Left		
SAR-LED-KITRP35	One Way, Right	SAR-LED-KITRP70	One Way, Right		
Structural Small		Structural Small			
STS-LED-KIT1P35	Type I	STS-LED-KIT1P70	Type I		
STS-LED-KIT2P35	Type II	STS-LED-KIT2P70	Type II		
STS-LED-KIT3P35	Type III	STS-LED-KIT3P70	Type III		
STS-LED-KIT4P35	Type IV	STS-LED-KIT4P70	Type IV		
STS-LED-KIT5P35	Type V	STS-LED-KIT5P70	Type V		
STS-LED-KITLP35	One Way, Left	STS-LED-KITLP70	One Way, Left		
STS-LED-KITRP35	One Way, Right	STS-LED-KITRP70	One Way, Right		
The Entablature Small		The Entablature Small			
SET-LED-KIT1P35	Type I	SET-LED-KIT1P70	Type I		
SET-LED-KIT2P35	Type II	SET-LED-KIT2P70	Type II		
SET-LED-KIT3P35	Type III	SET-LED-KIT3P70	Type III		
SET-LED-KIT4P35	Type IV	SET-LED-KIT4P70	Type IV		
SET-LED-KIT5P35	Type V	SET-LED-KIT5P70	Type V		
SET-LED-KITLP35	One Way, Left	SET-LED-KITLP70	One Way, Left		
SET-LED-KITRP35	One Way, Right	SET-LED-KITRP70	One Way, Right		

ELECTRICAL MODULE


WP9S/SAR/STS/SET			
	Source	Color Temp.	Voltages
60L	60 LEDs,	2K 580nm	120 120V
	65W for 350mA	3K 3000K	208 208V
	120 LEDs,	4K 4000K	240 240V
40L	130W for 700mA	5K 5000K	277 277V
	WP9S		347 347V
	40 LEDs,		480 480V
	45W for 350mA		
	SAR/STS/SET,		
	93W for 700mA		
	SAR/STS/SET		
LLF			
	Source	Color Temp.	Voltages
20L	20 LEDs,	2K 580nm	UV 120-277V
	21W for LLF10/40	3K 3000K	
16L	16 LEDs,	4K 4000K	
	17W for LLF20/30	5K 5000K	
12L	13W for LLF50/60		

Note: Refer to LED Upgrade Kit Spec Sheets for complete ordering information
Consult DLC Website for current qualified product listings.

PICOPRISM LED UPGRADE KIT
The Archetype (SAR) Shown



LED EmitterDeck




Electrical Module


PICOPRISM LED UPGRADE KIT
WARP9 (WP9S) Shown



LED EmitterDeck



Drilling Template



Electrical Module

HID to LED Upgrade Kit PicoPrism®

WP9L/AR/STL/ET/CC25

FEATURES

- Reduces energy consumption up to 50% compared to original HID source
- 350mA or 700mA current
- Maintains architectural relevance, application integrity and extends asset value
- 0-10V dimming interface, allowing 0-100% illumination output options
- Full palette of lighting distributions and color temperatures to match existing installations
- Preserves applicable UL/CSA/ETL product listing and manufacturer's warranty
- Compatible driver options for renewable energy systems
- Qualifies for many rebates and tax incentives



LED UPGRADE KIT

ORDERING INFORMATION (Example)

WP9L-LED-KIT3P70

120L5K240

CATALOG NUMBER


The Archetype Large 350mA		The Archetype Large 700mA		WARP9 Large 350mA		WARP9 Large 700mA	
AR-LED-KIT1P35	Type I	AR-LED-KIT1P70	Type I	WP9L-LED-KIT1P35	Type I	WP9L-LED-KIT1P70	Type I
AR-LED-KIT2P35	Type II	AR-LED-KIT2P70	Type II	WP9L-LED-KIT2P35	Type II	WP9L-LED-KIT2P70	Type II
AR-LED-KIT3P35	Type III	AR-LED-KIT3P70	Type III	WP9L-LED-KIT3P35	Type III	WP9L-LED-KIT3P70	Type III
AR-LED-KIT4P35	Type IV	AR-LED-KIT4P70	Type IV	WP9L-LED-KIT4P35	Type IV	WP9L-LED-KIT4P70	Type IV
AR-LED-KIT5P35	Type V	AR-LED-KIT5P70	Type V	WP9L-LED-KIT5P35	Type V	WP9L-LED-KIT5P70	Type V
AR-LED-KITLP35	One Way, Left	AR-LED-KITLP70	One Way, Left	WP9L-LED-KITLP35	One Way, Left	WP9L-LED-KITLP70	One Way, Left
AR-LED-KITRP35	One Way, Right	AR-LED-KITRP70	One Way, Right	WP9L-LED-KITRP35	One Way, Right	WP9L-LED-KITRP70	One Way, Right
Structural Large 350mA		Structural Large 700mA					
STL-LED-KIT1P35	Type I	STL-LED-KIT1P70	Type I				
STL-LED-KIT2P35	Type II	STL-LED-KIT2P70	Type II				
STL-LED-KIT3P35	Type III	STL-LED-KIT3P70	Type III				
STL-LED-KIT4P35	Type IV	STL-LED-KIT4P70	Type IV				
STL-LED-KIT5P35	Type V	STL-LED-KIT5P70	Type V				
STL-LED-KITLP70	One Way, Left	STL-LED-KITLP70	One Way, Left				
STL-LED-KITRP70	One Way, Right	STL-LED-KITRP70	One Way, Right				
The Entablature Large 350mA		The Entablature Large 700mA					
ET-LED-KIT1P35	Type I	ET-LED-KIT1P70	Type I				
ET-LED-KIT2P35	Type II	ET-LED-KIT2P70	Type II				
ET-LED-KIT3P35	Type III	ET-LED-KIT3P70	Type III				
ET-LED-KIT4P35	Type IV	ET-LED-KIT4P70	Type IV				
ET-LED-KIT5P35	Type V	ET-LED-KIT5P70	Type V				
ET-LED-KITLP35	One Way, Left	ET-LED-KITLP70	One Way, Left				
ET-LED-KITRP35	One Way, Right	ET-LED-KITRP70	One Way, Right				
Curvilinear 25" 350mA		Curvilinear 25" 700mA					
CC25-LED-KIT1P35	Type I	CC25-LED-KIT1P70	Type I				
CC25-LED-KIT2P35	Type II	CC25-LED-KIT2P70	Type II				
CC25-LED-KIT3P35	Type III	CC25-LED-KIT3P70	Type III				
CC25-LED-KIT4P35	Type IV	CC25-LED-KIT4P70	Type IV				
CC25-LED-KIT5P35	Type V	CC25-LED-KIT5P70	Type V				
CC25-LED-KITLP35	One Way, Left	CC25-LED-KITLP70	One Way, Left				
CC25-LED-KITRP35	One Way, Right	CC25-LED-KITRP70	One Way, Right				

ELECTRICAL MODULE


Source	Color Temp.	Voltages
120L 120 LEDs, 132W for 350mA WP9L	2K 580nm	120 120V
	3K 3000K	208 208V
	4K 4000K	240 240V
96L 96 LEDs, 106W for 350mA CC25 219W for 700mA CC25	5K 5000K	277 277V
		347 347V
80L 80 LEDs, 92W for 350mA AR/STL/ET 184-188W for 700mA AR/STL/ET		480 480V

Note: Refer to LED Upgrade Kit Spec Sheets for complete ordering information
Consult DLC Website for current qualified product listings.

PICOPRISM LED UPGRADE KIT
The Archetype (AR) Shown




PICOPRISM LED UPGRADE KIT
WARP9 (WP9L) Shown



HID to LED Upgrade Kit PicoEmitter®

WP9S/SAR/STS/SET/CC17/SRS1/NSL/BNS/RA17/BE17/AE17/LE19/WD14

LED UPGRADE KIT



FEATURES

- Reduces energy consumption up to 50% compared to original HID source
- 350mA current
- Maintains architectural relevance, application integrity and extends asset value
- 0-10V dimming interface, allowing 0-100% illumination output options
- Full palette of lighting distributions and color temperatures to match existing installations
- Preserves applicable UL/CUL/ETL product listing and manufacturer's warranty
- Compatible driver options for renewable energy systems
- Qualifies for many rebates and tax incentives



ORDERING INFORMATION (Example)

WP9S-LED-KIT3E35

60L5K240

CATALOG NUMBER


WARP9 Small	Curvilinear Small	Era Small	Wall Director Small
WP9S-LED-KIT1E35 Type I	CC17-LED-KIT1E35 Type I	RA17-LED-KIT1E35 Type I	WD14-LED-KIT2E35 Type II
WP9S-LED-KIT2E35 Type II	CC17-LED-KIT2E35 Type II	RA17-LED-KIT2E35 Type II	WD14-LED-KIT3E35 Type III
WP9S-LED-KIT3E35 Type III	CC17-LED-KIT3E35 Type III	RA17-LED-KIT3E35 Type III	WD14-LED-KIT4E35 Type IV
WP9S-LED-KIT4E35 Type IV	CC17-LED-KIT4E35 Type IV	RA17-LED-KIT4E35 Type IV	WD14-LED-KIT5E35 Type V
WP9S-LED-KIT5E35 Type V	CC17-LED-KIT5E35 Type V	RA17-LED-KIT5E35 Type V	WD14-LED-KITLE35 One Way, Left
WP9S-LED-KITLE35 One Way, Left	CC17-LED-KITLE35 One Way, Left	RA17-LED-KITLE35 One Way, Left	WD14-LED-KITRE35 One Way, Right
WP9S-LED-KITRE35 One Way, Right	CC17-LED-KITRE35 One Way, Right	RA17-LED-KITRE35 One Way, Right	
The Archetype Small	Solitaire Small	Era Bell Small	
SAR-LED-KIT1E35 Type I	SRS1-LED-KIT1E35 Type I	BE17-LED-KIT1E35 Type I	
SAR-LED-KIT2E35 Type II	SRS1-LED-KIT2E35 Type II	BE17-LED-KIT2E35 Type II	
SAR-LED-KIT3E35 Type III	SRS1-LED-KIT3E35 Type III	BE17-LED-KIT3E35 Type III	
SAR-LED-KIT4E35 Type IV	SRS1-LED-KIT4E35 Type IV	BE17-LED-KIT4E35 Type IV	
SAR-LED-KIT5E35 Type V	SRS1-LED-KIT5E35 Type V	BE17-LED-KIT5E35 Type V	
SAR-LED-KITLE35 One Way, Left	SRS1-LED-KITLE35 One Way, Left	BE17-LED-KITLE35 One Way, Left	
SAR-LED-KITRE35 One Way, Right	SRS1-LED-KITRE35 One Way, Right	BE17-LED-KITRE35 One Way, Right	
Structural Small	NeoSphere	Era Acorn Small	
STS-LED-KIT1E35 Type I	NSL-LED-KIT3E35 Type III	AE17-LED-KIT1E35 Type I	
STS-LED-KIT2E35 Type II	NSL-LED-KIT5E35 Type V	AE17-LED-KIT2E35 Type II	
STS-LED-KIT3E35 Type III		AE17-LED-KIT3E35 Type III	
STS-LED-KIT4E35 Type IV		AE17-LED-KIT4E35 Type IV	
STS-LED-KIT5E35 Type V		AE17-LED-KIT5E35 Type V	
STS-LED-KITLE35 One Way, Left		AE17-LED-KITLE35 One Way, Left	
STS-LED-KITRE35 One Way, Right		AE17-LED-KITRE35 One Way, Right	
The Entablature Small	Bounce	Era Lantern Small	
SET-LED-KIT1E35 Type I	BNS-LED-KIT1E35 Type I	LE19-LED-KIT1E35 Type I	
SET-LED-KIT2E35 Type II	BNS-LED-KIT2E35 Type II	LE19-LED-KIT2E35 Type II	
SET-LED-KIT3E35 Type III	BNS-LED-KIT3E35 Type III	LE19-LED-KIT3E35 Type III	
SET-LED-KIT4E35 Type IV	BNS-LED-KIT4E35 Type IV	LE19-LED-KIT4E35 Type IV	
SET-LED-KIT5E35 Type V	BNS-LED-KIT5E35 Type V	LE19-LED-KIT5E35 Type V	
SET-LED-KITLE35 One Way, Left	BNS-LED-KITLE35 One Way, Left	LE19-LED-KITLE35 One Way, Left	
SET-LED-KITRE35 One Way, Right	BNS-LED-KITRE35 One Way, Right	LE19-LED-KITRE35 One Way, Right	

ELECTRICAL MODULE

Source	Color Temp.	Voltages
60L 60 LEDs, 64-68W	2K 580nm	120 120V
	3K 3000K	208 208V
	4K 4000K	240 240V
	5K 5000K	277 277V
		347 347V
		480 480V

Note: Refer to LED Upgrade Kit Spec Sheets for complete ordering information
Consult DLC Website for current qualified product listings.

LED UPGRADE KIT WITH DRILLING TEMPLATES
The Archetype (SAR) Shown



LED UPGRADE KIT WITHOUT DRILLING TEMPLATES
Era (RA17) Shown




HID to LED Upgrade Kit PicoEmitter®

WP9L/AR/STL/ET/CC21/RA25/BE21/AE21/WD18

FEATURES

- Reduces energy consumption up to 50% compared to original HID source
- 350mA current
- Maintains architectural relevance, application integrity and extends asset value
- 0-10V dimming interface, allowing 0-100% illumination output options
- Full palette of lighting distributions and color temperatures to match existing installations
- Preserves applicable UL/CSA/ETL product listing and manufacturer's warranty
- Compatible driver options for renewable energy systems
- Qualifies for many rebates and tax incentives



LED UPGRADE KIT

ORDERING INFORMATION (Example)

WP9L-LED-KIT3E35


120L5K240

CATALOG NUMBER

WARP9 Large		Curvilinear Large		Era Large		Wall Director Large	
WP9L-LED-KIT1E35	Type I	CC21-LED-KIT1E35	Type I	RA25-LED-KIT1E35	Type I	WD18-LED-KIT2E35	Type II
WP9L-LED-KIT2E35	Type II	CC21-LED-KIT2E35	Type II	RA25-LED-KIT2E35	Type II	WD18-LED-KIT3E35	Type III
WP9L-LED-KIT3E35	Type III	CC21-LED-KIT3E35	Type III	RA25-LED-KIT3E35	Type III	WD18-LED-KIT4E35	Type IV
WP9L-LED-KIT4E35	Type IV	CC21-LED-KIT4E35	Type IV	RA25-LED-KIT4E35	Type IV	WD18-LED-KIT5E35	Type V
WP9L-LED-KIT5E35	Type V	CC21-LED-KIT5E35	Type V	RA25-LED-KIT5E35	Type V	WD18-LED-KITLE35	One Way, Left
WP9L-LED-KITLE35	One Way, Left	CC21-LED-KITLE35	One Way, Left	RA25-LED-KITLE35	One Way, Left	WD18-LED-KITRE35	One Way, Right
WP9L-LED-KITRE35	One Way, Right	CC21-LED-KITRE35	One Way, Right	RA25-LED-KITRE35	One Way, Right		
The Archetype Large				Era Bell Large			
AR-LED-KIT1E35	Type I			BE21-LED-KIT1E35	Type I		
AR-LED-KIT2E35	Type II			BE21-LED-KIT2E35	Type II		
AR-LED-KIT3E35	Type III			BE21-LED-KIT3E35	Type III		
AR-LED-KIT4E35	Type IV			BE21-LED-KIT4E35	Type IV		
AR-LED-KIT5E35	Type V			BE21-LED-KIT5E35	Type V		
AR-LED-KITLE35	One Way, Left			BE21-LED-KITLE35	One Way, Left		
AR-LED-KITRE35	One Way, Right			BE21-LED-KITRE35	One Way, Right		
Structural Large				Era Acorn Large			
STL-LED-KIT1E35	Type I			AE21-LED-KIT1E35	Type I		
STL-LED-KIT2E35	Type II			AE21-LED-KIT2E35	Type II		
STL-LED-KIT3E35	Type III			AE21-LED-KIT3E35	Type III		
STL-LED-KIT4E35	Type IV			AE21-LED-KIT4E35	Type IV		
STL-LED-KIT5E35	Type V			AE21-LED-KIT5E35	Type V		
STL-LED-KITLE35	One Way, Left			AE21-LED-KITLE35	One Way, Left		
STL-LED-KITRE35	One Way, Right			AE21-LED-KITRE35	One Way, Right		
The Entablature Large						ELECTRICAL MODULE	
ET-LED-KIT1E35	Type I					Source	Color Temp.
ET-LED-KIT2E35	Type II					120L 120 LEDs,	2K 580nm
ET-LED-KIT3E35	Type III					126-133W	3K 3000K
ET-LED-KIT4E35	Type IV					96L 96 LEDs,	4K 4000K
ET-LED-KIT5E35	Type V					103W for ET	5K 5000K
ET-LED-KITLE35	One Way, Left						120 120V
ET-LED-KITRE35	One Way, Right						208 208V
							240 240V
							277 277V
							347 347V
							480 480V

Note: Refer to LED Upgrade Kit Spec Sheets for complete ordering information
Consult DLC Website for current qualified product listings.

LED UPGRADE KIT WITH DRILLING TEMPLATES
The Archetype (AR) Shown



LED UPGRADE KIT WITHOUT DRILLING TEMPLATES
Era (RA25) Shown

