


Wall Director

Small Housing Scale - WD2S

Wall Mounted



FEATURES

- -5° to +10° tilt adjustment
- High performance optics deliver up to 8,500 lumens
- Sleek architectural form factor
- Diffused lens option
- Programmable occupancy sensor (dimming)
- NX and SiteSync wireless controls
- 130+ lumens per watt
- IES and flood distributions available
- Optional inverted/up mounting



ORDERING INFORMATION (Example)

WDS	D	24L	30	3K7	3	120	GT
FIXTURE	MOUNTING	SOURCE	WATTAGE	LIGHT ENGINE	DISTRIBUTION	VOLTAGE	FINISH
WDS Wall Director Small	D Down U ¹ Up	24L 24 LEDs	30 30 Watts 40 40 Watts 60 60 Watts 75 75 Watts	3K7 3000K/70CRI 3K8 3000K/80CRI 4K7 4000K/70CRI 4K8 4000K/80CRI 5K7 5000K/70CRI	1 Type I 2 Type II 3 Type III 4W Type IV Wide 4F Type IV Forward SP Spot/Column WG ² Wall Graze FTD ² Front Throw Diffused WTD ² Wide Throw Diffused	UNV 120-277V 347 ³ 347V 480 ³ 480V	BL Black DB Dark Bronze LG Light Gray GT Graphite PS Platinum Silver TT Titanium WH White CC Custom Color

PC
CONTROL OPTIONS
PC Button Photocell
SCP-8F Programmable Occ. Sensor (<9' height)
SCP-20F Programmable Occ. Sensor (9' - 20' height)
SWP ³ SiteSync Wireless Pre-Commission
SWPM ³ SiteSync Wireless w/Occupancy Sensor Pre-Commission
NXWE ⁵ NX Wireless Enabled

EM
OPTIONS
EM ⁴ Integral Emergency Battery Backup
SF Single Fuse & Fuse holder
DF Double Fuse & Fuse holder

SWUSB
ACCESSORIES
SCPREMOTE SCP configuration tool
SWUSB SiteSync Software on USB
SWTAB SiteSync Windows® Tablet
SWBRG SiteSync Software Bridge Node

Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

¹ Not available with EM option or with SCP & SWPM sensor options
² WG, FTD, and WTD come with a diffused lens.
³ 60 and 75 watt versions only
⁴ Universal voltage only (120-277), not available with PC option
⁵ 120-347V only

