

High Performance LED Remote

FEATURES

- High performance LED remote designed for indoor/outdoor applications
- Sturdy, ADA compliant, vandal resistant, die-cast aluminum construction
- Four long-life, high-output 4000K LEDs configured in redundant pairs
- Design optimized for wide area illumination pattern with no heads to aim
- 90-minute emergency operation from external 6-12V DC source
- U.S. Patent No. D627,916



REMOTE HEADS AND FIXTURES

ORDERING INFORMATION

PGR

MODEL

FINISH

- W White
- B Black
- Z Dark Bronze
- P Platinum Silver

INPUT POWER REQUIREMENTS

- 12 watts at 6vDC, 13 watts at 12vDC

SPECIFIC LED INFORMATION

- Lamp Color: Neutral White, 4000K
- Color Rendering Index (CRI): 75
- Total Lamp Output: 445 Lumens min. Initial
- LED Lamplife: 48,000 hrs. at 70% of Initial

