

NOTES:

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 12VDC (12-15 ADJ)


AMP RATING: 15A

OUTPUT POWER: 180W

EFFICIENCY: 88%

OPERATING TEMP.: -20°C TO +60°C

FREQUENCY: 47-63Hz

PROPRIETARY AND CONFIDENTIAL		NAME		DATE		 Acme Electric® MENOMONEE FALLS, WI 53051 USA		
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.		DRAWN	AJP	11-21-17				
DO NOT SCALE DRAWING		CHECKED	AJP	11-21-17				
		ENG APPR.	AJP	11-21-17				
SCALE: 1:2				TITLE: SLIMLINE SINGLE PHASE				
SHEET 1 OF 1			SIZE	DWG. NO.	REV			
			B	DM11215S	A			