



NOTES:

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 24VDC (24-28 ADJ)

AMP RATING: 3.4-2.8A

OUTPUT POWER: 80W

EFFICIENCY: 90%

OPERATING TEMP.: -20°C TO +60°C

FREQUENCY: 47-63Hz

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.

DO NOT SCALE DRAWING

	NAME	DATE	 <p>MENOMONEE FALLS, WI 53051 USA</p>	
DRAWN	AJP	11-21-17		
CHECKED	AJP	11-21-17		
ENG APPR.	AJP	11-21-17		
TITLE:			SLIMLINE SINGLE PHASE	
SCALE: 1:2			SIZE	DWG. NO.
SHEET 1 OF 1			B	DM124033S
			REV	A