



NOTES:

VOLTAGE RANGE AC: 90-254VAC

OUTPUT VOLTAGE: 48VDC (46-52 ADJ)

AMP RATING: 1.25-1.15A

OUTPUT POWER: 60W

EFFICIENCY: 89%

OPERATING TEMP.: -10°C TO +60°C

FREQUENCY: 47-63Hz

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.
 DO NOT SCALE DRAWING

	NAME	DATE	 MENOMONEE FALLS, WI 53051 USA	
DRAWN	AJP	11-21-17		
CHECKED	AJP	11-21-17		
ENG APPR.	AJP	11-21-17		
TITLE:			SINGLE PHASE	
SCALE: 1:2			SIZE	DWG. NO.
SHEET 1 OF 1			B	DM1480125
			REV	A