



NOTES:

VOLTAGE RANGE DC: 450-820VDC

OUTPUT VOLTAGE: 24VDC (24-28 ADJ)

AMP RATING: 5.0-4.3A

OUTPUT POWER: 120W

EFFICIENCY: 89%

OPERATING TEMP.: -10 °C TO +60 °C

FREQUENCY: 47-63Hz

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.

DO NOT SCALE DRAWING

	NAME	DATE	 Acme Electric [®] MENOMONEE FALLS, WI 53051 USA		
DRAWN	AJP	11-21-17			
CHECKED	AJP	11-21-17			
ENG APPR.	AJP	11-21-17			
SCALE: 1:2			TITLE: THREE PHASE		
SHEET 1 OF 1			SIZE	DWG. NO.	REV
			B	DM32405	A