



**NOTES:**

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 12VDC (10-14 ADJ)

AMP RATING: 5.0-3.57A

OUTPUT POWER: 50W

EFFICIENCY: 83%

OPERATING TEMP.: -10°C TO +50°C

FREQUENCY: 47-63Hz

	NAME	DATE	 <p><b>Acme Electric</b><sup>®</sup> MENOMONEE FALLS, WI 53051 USA</p>	
DRAWN	AJP	11-21-17		
CHECKED	AJP	11-21-17		
ENG APPR.	AJP	11-21-17		
TITLE:			PLASTIC	
SCALE: 1:2		SIZE	DWG. NO.	REV
SHEET 1 OF 1		<b>B</b>	DMP11204	<b>A</b>

**PROPRIETARY AND CONFIDENTIAL**  
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.  
 DO NOT SCALE DRAWING