

**NOTES:**

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 15VDC (14-18 ADJ)


AMP RATING: 2.14-1.67A

OUTPUT POWER: 30W

EFFICIENCY: 84%

OPERATING TEMP.: -10°C TO +50°C

FREQUENCY: 47-63Hz

	NAME	DATE	 <p><b>Acme Electric</b> MENOMONEE FALLS, WI 53051 USA</p>	
DRAWN	AJP	11-21-17		
CHECKED	AJP	11-21-17		
ENG APPR.	AJP	11-21-17		
TITLE:			PLASTIC	
SCALE: 1:2			SIZE	DWG. NO.
SHEET 1 OF 1			<b>B</b>	DMP11502
DO NOT SCALE DRAWING			REV	<b>A</b>

**PROPRIETARY AND CONFIDENTIAL**  
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.