

NOTES:

VOLTAGE RANGE AC: 90-264VAC

OUTPUT VOLTAGE: 24VDC (22-28 ADJ)


AMP RATING: 1.36-1.07A

OUTPUT POWER: 30W

EFFICIENCY: 85%

OPERATING TEMP.: -10°C TO +50°C

FREQUENCY: 47-63Hz

	NAME	DATE	 <p>Acme Electric MENOMONEE FALLS, WI 53051 USA</p>	
DRAWN	AJP	11-21-17		
CHECKED	AJP	11-21-17		
ENG APPR.	AJP	11-21-17		
<p>SCALE: 1:2</p>			TITLE: PLASTIC	
SHEET 1 OF 1		SIZE B	DWG. NO. DMP1240125	REV A

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.
DO NOT SCALE DRAWING