

HCMPT300TS (WITH TRANSFER SWITCH), Rev. B - Across-The-Line Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25	HCMPTF300TS1A.pdf	HCMPTF300TS1A.pdf	HCMPTF300TS1A.pdf	HCMPTF300TS1A.pdf	HCMPTF300TS1A.pdf	
30	HCMPTF300TS2B.pdf	HCMPTF300TS2B.pdf	HCMPTF300TS2B.pdf	HCMPTF300TS2B.pdf	HCMPTF300TS2B.pdf	
40	HCMPTS300TSA .pdf	HCMPTS300TSA .pdf	HCMPTS300TSA .pdf	HCMPTS300TSA .pdf	HCMPTS300TSA .pdf	
50						
60						
75						
100						
125						
150	HCMPTF300TS41A.pdf	HCMPTF300TS41A.pdf	HCMPTF300TS41A.pdf			
200	HCMPTF300TS42B.pdf	HCMPTF300TS42B.pdf	HCMPTF300TS42B.pdf			
250	HCMPTS300TS4A .pdf	HCMPTS300TS4A .pdf	HCMPTS300TS4A .pdf	HCMPTF300TS41A.pdf	HCMPTF300TS41A.pdf	
300				HCMPTF300TS42B.pdf	HCMPTF300TS42B.pdf	
350				HCMPTS300TS4A .pdf	HCMPTS300TS4A .pdf	
400						
450						
500						
600						

HCMPT300 (WITHOUT TRANSFER SWITCH), Rev. B - Across-The-Line Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25						
30						
40						
50						
60						
75						
100	HCMPTF3001A.pdf	HCMPTF3001A.pdf	HCMPTF3001A.pdf	HCMPTF3001A.pdf	HCMPTF3001A.pdf	HCMPTF3001A.pdf
125	HCMPTF3002B.pdf	HCMPTF3002B.pdf	HCMPTF3002B.pdf	HCMPTF3002B.pdf	HCMPTF3002B.pdf	HCMPTF3002B.pdf
150	HCMPTS300A .pdf	HCMPTS300A .pdf	HCMPTS300A .pdf	HCMPTS300A .pdf	HCMPTS300A .pdf	HCMPTS300A .pdf
200						
250						
300						
350						
400						
450						
500						
600						

HCMPT400TS (WITH TRANSFER SWITCH), Rev. B - Primary Resistance Starter FPC						
HP	VOLTAGE					
	200	208	230	380	480	575
15	HCMPTF400TS1A.pdf HCMPTF400TS2B.pdf HCMPTS400TSA .pdf	HCMPTF400TS1A.pdf HCMPTF400TS2B.pdf HCMPTS400TSA .pdf	HCMPTF400TS1A.pdf HCMPTF400TS2B.pdf HCMPTS400TSA .pdf	HCMPTF400TS1A.pdf HCMPTF400TS2B.pdf HCMPTS400TSA .pdf	HCMPTF400TS1A.pdf HCMPTF400TS2B.pdf HCMPTS400TSA .pdf	
20						
25						
30						
40						
50						
60						
75						
100						
125						
150	HCMPTF400TS41A.pdf	HCMPTF400TS41A.pdf HCMPTF400TS42B.pdf HCMPTS400TS4A .pdf	HCMPTF400TS41A.pdf HCMPTF400TS42B.pdf HCMPTS400TS4A .pdf	HCMPTF400TS41A.pdf HCMPTF400TS42B.pdf HCMPTS400TS4A .pdf	HCMPTF400TS41A.pdf HCMPTF400TS42B.pdf HCMPTS400TS4A .pdf	
200						
250	HCMPTF400TS42B.pdf HCMPTS400TS4A .pdf					
300						
350						
400						
450						
500						
600						

HCMPT400 (WITHOUT TRANSFER SWITCH), Rev. B - Primary Resistance Starter FPC						
HP	VOLTAGE					
	200	208	230	380	480	575
15	HCMPTF4001A.pdf HCMPTF4002B.pdf HCMPTS400A .pdf	HCMPTF4001A.pdf HCMPTF4002B.pdf HCMPTS400A .pdf	HCMPTF4001A.pdf HCMPTF4002B.pdf HCMPTS400A .pdf	HCMPTF4001A.pdf HCMPTF4002B.pdf HCMPTS400A .pdf	HCMPTF4001A.pdf HCMPTF4002B.pdf HCMPTS400A .pdf	HCMPTF4001A.pdf HCMPTF4002B.pdf HCMPTS400A .pdf
20						
25						
30						
40						
50						
60						
75						
100						
125						
150						
200						
250						
300						
350						
400						
450						
500						
600						

HCMPT420TS (WITH TRANSFER SWITCH), Rev. B - Part Winding Starter FPC						
HP	VOLTAGE					
	200	208	230	380	480	575
15						
20						
25						
30	HCMPTF420TS1A.pdf	HCMPTF420TS1A.pdf	HCMPTF420TS1A.pdf	HCMPTF420TS1A.pdf	HCMPTF420TS1A.pdf	
40	HCMPTF420TS2B.pdf	HCMPTF420TS2B.pdf	HCMPTF420TS2B.pdf	HCMPTF420TS2B.pdf	HCMPTF420TS2B.pdf	
50	HCMPTS420TSA .pdf	HCMPTS420TSA .pdf	HCMPTS420TSA .pdf	HCMPTS420TSA .pdf	HCMPTS420TSA .pdf	
60						
75						
100						
125						
150	HCMPTF420TS41A.pdf					
200	HCMPTF420TS42B.pdf	HCMPTF420TS41A.pdf	HCMPTF420TS41A.pdf			
250	HCMPTS420TS4A .pdf	HCMPTF420TS42B.pdf	HCMPTF420TS42B.pdf	HCMPTF420TS41A.pdf		
300		HCMPTS420TS4A .pdf	HCMPTS420TS4A .pdf	HCMPTS420TS4A .pdf	HCMPTF420TS41A.pdf	
350					HCMPTF420TS42B.pdf	
400					HCMPTS420TS4A .pdf	
450						
500						
600						

HCMPT420 (WITHOUT TRANSFER SWITCH), Rev. B - Part Winding Starter FPC						
HP	VOLTAGE					
	200	208	230	380	480	575
15						
20						
25						
30						
40						
50						
60						
75						
100	HCMPTF4201A.pdf	HCMPTF4201A.pdf	HCMPTF4201A.pdf	HCMPTF4201A.pdf	HCMPTF4201A.pdf	HCMPTF4201A.pdf
125	HCMPTF4202B.pdf	HCMPTF4202B.pdf	HCMPTF4202B.pdf	HCMPTF4202B.pdf	HCMPTF4202B.pdf	HCMPTF4202B.pdf
150	HCMPTS420A .pdf	HCMPTS420A .pdf	HCMPTS420A .pdf	HCMPTS420A .pdf	HCMPTS420A .pdf	HCMPTS420A .pdf
200						
250						
300						
350						
400						
450						
500						
600						

HCMPT430TS (WITH TRANSFER SWITCH), Rev. B - Wye-Delta Open Transition Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20	HCMPTF430TS1A.pdf					
25	HCMPTF430TS2B.pdf	HCMPTF430TS1A.pdf	HCMPTF430TS1A.pdf			
30	HCMPTS430TSA .pdf	HCMPTF430TS2B.pdf	HCMPTF430TS2B.pdf	HCMPTF430TS1A.pdf	HCMPTF430TS1A.pdf	
40	HCMPTM430TSA .pdf	HCMPTS430TSA .pdf	HCMPTS430TSA .pdf	HCMPTF430TS2B.pdf	HCMPTF430TS2B.pdf	
50		HCMPTM430TSA .pdf	HCMPTM430TSA .pdf	HCMPTS430TSA .pdf	HCMPTS430TSA .pdf	
60				HCMPTM430TSA .pdf	HCMPTM430TSA .pdf	
75						
100						
125						
150	HCMPTF430TS41A.pdf					
200	HCMPTF430TS42B.pdf	HCMPTF430TS41A.pdf	HCMPTF430TS41A.pdf			
250	HCMPTS430TS4A .pdf	HCMPTF430TS42B.pdf	HCMPTF430TS42B.pdf	HCMPTF430TS41A.pdf		
300	HCMPTM430TS4A .pdf	HCMPTS430TS4A .pdf	HCMPTS430TS4A .pdf	HCMPTF430TS42B.pdf	HCMPTF430TS41A.pdf	
350		HCMPTM430TS4A .pdf	HCMPTM430TS4A .pdf	HCMPTS430TS4A .pdf	HCMPTF430TS42B.pdf	
400				HCMPTM430TS4A .pdf	HCMPTS430TS4A .pdf	
450					HCMPTM430TS4A .pdf	
500						
600						

HCMPT430 (WITHOUT TRANSFER SWITCH), Rev. B - Wye-Delta Open Transition Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25						
30						
40						
50						
60						
75	HCMPTF4301A.pdf	HCMPTF4301A.pdf	HCMPTF4301A.pdf	HCMPTF4301A.pdf	HCMPTF4301A.pdf	HCMPTF4301A.pdf
100	HCMPTF4302B.pdf	HCMPTF4302B.pdf	HCMPTF4302B.pdf	HCMPTF4302B.pdf	HCMPTF4302B.pdf	HCMPTF4302B.pdf
125	HCMPTS430A.pdf	HCMPTS430A.pdf	HCMPTS430A.pdf	HCMPTS430A.pdf	HCMPTS430A.pdf	HCMPTS430A.pdf
150	HCMPTM430A .pdf	HCMPTM430A .pdf	HCMPTM430A .pdf	HCMPTM430A .pdf	HCMPTM430A .pdf	HCMPTM430A .pdf
200						
250						
300						
350						
400						
450						
500						
600						

HCMPT435TS (WITH TRANSFER SWITCH), Rev. B - Wye-Delta Closed Transition Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20	HCMPTF435TS1A.pdf					
25	HCMPTF435TS2B.pdf	HCMPTF435TS1A.pdf	HCMPTF435TS1A.pdf			
30	HCMPTS435TSA .pdf	HCMPTF435TS2B.pdf	HCMPTF435TS2B.pdf	HCMPTF435TS1A.pdf	HCMPTF435TS1A.pdf	
40	HCMPTM435TSA .pdf	HCMPTS435TSA .pdf	HCMPTS435TSA .pdf	HCMPTF435TS2B.pdf	HCMPTF435TS2B.pdf	
50		HCMPTM435TSA .pdf	HCMPTM435TSA .pdf	HCMPTS435TSA .pdf	HCMPTS435TSA .pdf	
60				HCMPTM435TSA .pdf	HCMPTM435TSA .pdf	
75						
100						
125						
150	HCMPTF435TS41A.pdf					
200	HCMPTF435TS42B.pdf	HCMPTF435TS41A.pdf	HCMPTF435TS41A.pdf			
250	HCMPTS435TS4A .pdf	HCMPTF435TS42B.pdf	HCMPTF435TS42B.pdf	HCMPTF435TS41A.pdf		
300	HCMPTM435TS4A .pdf	HCMPTS435TS4A .pdf	HCMPTS435TS4A .pdf	HCMPTF435TS42B.pdf	HCMPTF435TS41A.pdf	
350		HCMPTM435TS4A .pdf	HCMPTM435TS4A .pdf	HCMPTS435TS4A .pdf	HCMPTF435TS42B.pdf	
400				HCMPTM435TS4A .pdf	HCMPTS435TS4A .pdf	
450					HCMPTM435TS4A .pdf	
500						
600						

HCMPT435 (WITHOUT TRANSFER SWITCH), Rev. B - Wye-Delta Closed Transition Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25						
30						
40						
50						
60						
75	HCMPTF4351A.pdf	HCMPTF4351A.pdf	HCMPTF4351A.pdf	HCMPTF4351A.pdf	HCMPTF4351A.pdf	HCMPTF4351A.pdf
100	HCMPTF4352B.pdf	HCMPTF4352B.pdf	HCMPTF4352B.pdf	HCMPTF4352B.pdf	HCMPTF4352B.pdf	HCMPTF4352B.pdf
125	HCMPTS435A.pdf	HCMPTS435A.pdf	HCMPTS435A.pdf	HCMPTS435A.pdf	HCMPTS435A.pdf	HCMPTS435A.pdf
150	HCMPTM435A .pdf	HCMPTM435A .pdf	HCMPTM435A .pdf	HCMPTM435A .pdf	HCMPTM435A .pdf	HCMPTM435A .pdf
200						
250						
300						
350						
400						
450						
500						
600						

HCMPT450TS (WITH TRANSFER SWITCH), Rev. B - Autotransformer Closed Transition Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25	HCMPTF450TS1A.pdf	HCMPTF450TS1A.pdf	HCMPTF450TS1A.pdf	HCMPTF450TS1A.pdf	HCMPTF450TS1A.pdf	
30	HCMPTF450TS2B.pdf	HCMPTF450TS2B.pdf	HCMPTF450TS2B.pdf	HCMPTF450TS2B.pdf	HCMPTF450TS2B.pdf	
40	HCMPTS450TSA .pdf	HCMPTS450TSA .pdf	HCMPTS450TSA .pdf	HCMPTS450TSA .pdf	HCMPTS450TSA .pdf	
50						
60						
75						
100						
125						
150	HCMPTF450TS41A.pdf					
200	HCMPTF450TS42B.pdf	HCMPTF450TS41A.pdf	HCMPTF450TS41A.pdf			
250	HCMPTS450TS4A .pdf	HCMPTF450TS42B.pdf	HCMPTF450TS42B.pdf	HCMPTF450TS41A.pdf		
300		HCMPTS450TS4A .pdf	HCMPTS450TS4A .pdf	HCMPTS450TS4A .pdf	HCMPTF450TS41A.pdf	
350					HCMPTF450TS42B.pdf	
400					HCMPTS450TS4A .pdf	
450						
500						
600						

HCMPT450 (WITHOUT TRANSFER SWITCH), Rev. B - Autotransformer Closed Transition Starter FPC

VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25						
30						
40						
50						
60						
75						
100	HCMPTF4501A.pdf	HCMPTF4501A.pdf	HCMPTF4501A.pdf	HCMPTF4501A.pdf	HCMPTF4501A.pdf	HCMPTF4501A.pdf
125	HCMPTF4502B.pdf	HCMPTF4502B.pdf	HCMPTF4502B.pdf	HCMPTF4502B.pdf	HCMPTF4502B.pdf	HCMPTF4502B.pdf
150	HCMPTS450A .pdf	HCMPTS450A .pdf	HCMPTS450A .pdf	HCMPTS450A .pdf	HCMPTS450A .pdf	HCMPTS450A .pdf
200						
250						
300						
350						
400						
450						
500						
600						

HCMPT700TS (WITH TRANSFER SWITCH), Rev. B - Soft Start/Stop Starter FPC						
VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25	HCMPTF700TS1A.pdf	HCMPTF700TS1A.pdf	HCMPTF700TS1A.pdf			
30	HCMPTF700TS2B.pdf	HCMPTF700TS2B.pdf	HCMPTF700TS2B.pdf	HCMPTF700TS1A.pdf		
40	HCMPTS700TSA .pdf	HCMPTS700TSA .pdf	HCMPTS700TSA .pdf	HCMPTF700TS2B.pdf	HCMPTF700TS1A.pdf	
50				HCMPTS700TSA .pdf	HCMPTF700TS2B.pdf	
60					HCMPTS700TSA .pdf	
75						
100						
125						
150	HCMPTF700TS41A.pdf					
200	HCMPTF700TS42B.pdf	HCMPTF700TS41A.pdf	HCMPTF700TS41A.pdf			
250	HCMPTS700TS4A .pdf	HCMPTF700TS42B.pdf	HCMPTF700TS42B.pdf	HCMPTF700TS41A.pdf		
300		HCMPTS700TS4A .pdf	HCMPTS700TS4A .pdf	HCMPTF700TS41A.pdf	HCMPTF700TS41A.pdf	
350				HCMPTF700TS42B.pdf	HCMPTF700TS42B.pdf	
400				HCMPTS700TS4A .pdf	HCMPTS700TS4A .pdf	
450						
500						
600						

HCMPT700 (WITHOUT TRANSFER SWITCH), Rev. B - Soft Start/Stop Starter FPC						
VOLTAGE						
HP	200	208	230	380	480	575
15						
20						
25						
30						
40						
50						
60						
75						
100	HCMPTF7001A.pdf	HCMPTF7001A.pdf	HCMPTF7001A.pdf	HCMPTF7001A.pdf	HCMPTF7001A.pdf	HCMPTF7001A.pdf
125	HCMPTF7002B.pdf	HCMPTF7002B.pdf	HCMPTF7002B.pdf	HCMPTF7002B.pdf	HCMPTF7002B.pdf	HCMPTF7002B.pdf
150	HCMPTS700A .pdf	HCMPTS700A .pdf	HCMPTS700A .pdf	HCMPTS700A .pdf	HCMPTS700A .pdf	HCMPTS700A .pdf
200						
250						
300						
350						
400						
450						
500						
600						