


INSTALLATION INSTRUCTIONS

CATALOG NUMBER

M2P-LED

POLES BY OTHERS USE (2) S/S 3/8-16 HEX NUTS AND S/S LOCK WASHERS. ACCESS IN POLE MAY BE REQUIRED 180° FROM FIXTURE ARM MOUNTING.


A.A.L. POLES ONLY PROVIDED WITH (2) 3/8-16 THREADED INSERTS AS SHOWN.



SEE NOTE#11

INSTALLATIONS STEPS:

- 1: TURN OFF ALL POWER.
- 2: OPEN DOOR FRAME, DISCONNECT LED ASSEMBLY REMOVE DOOR FRAME FROM HOUSING AND SET ASIDE.
- 3: REMOVE DRIVER ASS'Y AS SHOWN, FOR ACCESS TO MOUNTING.
- 4: SECURE TWO THREADED S/S STUDS INTO POLE THREADED INSERTS.
- 5: FEED WIRE LEADS FROM POLE OUT THROUGH WIREWAY HOLE FOR CONNECTION TO FIXTURE
- 6: PLACE THE ARM OVER THE THREADED STUDS, SO THAT THE CONTOURED END OF THE ARM IS AGAINST THE POLE.
- 7: SECURE WITH (2) HEX NUTS AND LOCKWASHERS AS SHOWN.
- 8: MAKE WIRE CONNECTIONS INSIDE OF FIXTURE AS REQUIRED PER CODE.
- 9: RETURN THE DOOR FRAME TO IT'S ORIGINAL POSITION AND SECURE IN PLACE.
- 10: CONNECT LED ASSEMBLY TO THE DRIVER ASSEMBLY.
- 11: MAKE WIRE CONNECTIONS AT BASE OF POLE TO INCOMING POWER SOURCE. **(NOTE: MAKE SURE GROUND ASSEMBLY TO THE EQUIPMENT GROUND).**
- 12: INSTALLATION IS COMPLETE.



TO INCOMING
POWER SOURCE