


RA-WM-ACC WALL MOUNT

RATIO ACCESSORY



Mounting Notes:

1. Position the wall mount plate over the Junction Box onto mounting surface in desired position and mark surface for (4) mounting holes.
2. At marked positions, drill and install (4) 3/8-16 to 1/2-13 wall anchors (not provided) that are appropriate for use with the surface material.
3. Route the power leads from the fixture through the tenon of the wall mount tenon and into the junction box. Make the wiring connections.
4. Place the wall mount onto the mounting surface and align with anchors. Using (4) fasteners, secure accessory to mounting surface.
5. Use RTV Silicone to caulk around the perimeter of the wall plate, creating a water-tight seal.
6. Mount fixture to the wall mount and tighten (4) 3/8-16 set screws of mast arm fitter assuring fixture is level. Tighten set screws to 12 ft.-lbs. torque.

Shipping Package Contents:

Wall Adapter Adapter

Material: Aluminum

Finish: Powdercoat Paint

Weight: 1.4 lbs

Hubbell Lighting
701 Millennium Blvd.
Greenville, SC 29607

Technical Support: (864) 678-1000
Fax: (864) 898-1065
www.hubbell.com

Catalog Number: RARWBXX
Instruction Sheet: 93099925 Rev A