



## EL201 - Path or Border Light Installation Instructions

**INSTRUCTIONS PERTAINING TO A RISK OF FIRE, OR INJURY TO PERSONS**  
**IMPORTANT SAFETY INSTRUCTIONS!**

**⚠ WARNING:** Fixtures must be grounded in accordance with local codes or the National Electrical Code. Portable Spear Mounts using a cord and plug must be plugged into a receptacle protected by a Ground Fault Circuit Interrupter (G.F.C.I.) in accordance with the National Electrical Code. Failure to take these steps may result in serious personal injury.

**CAUTION:** Lighted lamp is HOT! Do not touch hot lens, guard or enclosure. Fixtures are approved for above grade installation only.


**MAINTENANCE:** To maintain light efficiency and prevent fixture overheating, lenses must be kept clean and free of dirt, dust, leaves, trash and mineral deposits from water. **DO NOT** operate luminaire with missing or damaged lens. **KEEP THIS SHEET FOR FUTURE REFERENCE.**

Your Kim fixture is supplied with ½" NPT male mounting threads.

**Tools Required:**  Thread Sealant  Flat Blade Screwdriver

**INSTALLATION INSTRUCTIONS:**


**⚠** Make certain electrical supply is **OFF** before starting fixture installation.




1. Pull fixture leads through stem and attach fixture head.



2. Install stem, coating exposed threads with thread sealant to keep moisture from entering junction box.




3. Attach fixture leads to circuit leads observing polarity, i.e.; green-to-ground, white-to-common and black-to-voltage.



4. To install lamp, remove screws, cover, spacers or louvers and globe.



5. Install lamp of type and wattage as shown on fixture label and chart below.



6. Replace globe, spacers or louvers, cover and screws.

LAMP INFORMATION		
CAT. NO.	LAMP TYPE	WATTS
EL120	A21	100
EL121	A19	75

• See [HLI Standard Warranty](#) for additional information