

### Power and Style in Hard-to-Reach Places!

- Brushed aluminum or brushed brass plated
- Round cover for easy mounting and orientation
- Low profile cover
- Perfect for spaces without wall outlets

Bryant's die-cast aluminum floor box covers are now available in two new finishes: brushed aluminum and brushed brass plated to complement a variety of interiors. These covers feature a recessed design that enables the access door to be closed while in use, minimizing plug protrusion and allowing furniture to be located over the plug. The push-in-place leveling system makes slab-on-grade installations a simple and adjustable process.

Bryant's floor box outlets comply with NEC® code 210.52 which states that floor receptacles can count as part of the required number of outlets when located within 18 inches of a wall. Floor boxes provide aesthetic, readily-available power and are especially beneficial in places where wall outlets are not always an option such as along glass exterior walls or in larger rooms.



#### FEATURES

- Recessed design minimizes plug protrusion
- Post-pour adjustability
- Line and low voltage options

#### SPECIFICATIONS

- Flange height 0.12 inch, diameter 6.00 inch
- Two openings for cable egress
- Plated die-cast aluminum
- 4 inch minimum concrete pour

#### STANDARDS/LISTINGS/VERIFICATIONS

- Box and Cover - Complies with UL Listing 514C for scrub water test
- Complies with ADA Standards for Accessible Design Section 4.5.2 - Changes in Level
- Load tested to withstand up to 300 lbs
- UL Listed E92074 floor box

#### APPLICATIONS

- Large family rooms
- Entertainment centers
- Near glass partition walls
- Underneath furniture



#### FLOOR BOXES ALSO FROM BRYANT

- Solid brass and thermoplastic
- Available in black, chestnut brown, and ivory



