

FCR Series Premium Rack Mount Solution

Next generation enclosures expand capacity and access

Hubbell's FCR enclosures feature enhancements to capacity, cable management and administration. The 17-inch depth maximizes space for interconnections, splice trays and cable storage. The L-shaped slide-out cover permits full internal access, while improving dust shielding and tamper resistance. A user-friendly clip-on labeling system facilitates administration and accepts user-generated labels. Cable management features and hardware maintain cable bend radius for standards-compliant installation.

FEATURES


- 17-inch depth relieves cable congestion
- Easy access slide-out top
- Patented cable bend relief bezels
- Easy entry rear grommets
- User-friendly clip-on labeling
- Magnetic door latch (2U, 3U, 4U)
- Slide out inner drawer allows for maximum access
- Easy access plunger secures tray
- 16 gauge steel construction
- 19" and 23" rack mount options
- 9SP available in the 2U staggered configuration



Vertical Panel Mounting
FCR2U9SP and FCR4U15SP

Compatibility

- Hubbell FSP panels
- OC Series cassettes
- OC Series splice cassettes




FCR Series Premium Rack Mount Solution



FCR Series Enclosures

Configuration	FSP Panels	Splice Trays	Maximum LC Ports	Catalog No.
1U	3	3	72	FCR1U3SP
1U, Locking	3	3	72	FCR1U3SPL
2U	6	6	144	FCR2U6SP
2U, Locking	6	6	144	FCR2U6SPL
2U	6	6	216	FCR2U9SP
2U, Locking	6	6	216	FCR2U9SPL
3U	12	12	288	FCR3U12SP
4U	15	16	360	FCR4U15SP
4U, Locking	15	16	360	FCR4U15SPL



Our Most Popular FSP Adapter Panels

- Premium zirconia ceramic components
- Multimode or singlemode use

FSP Adapter Panels

Ports	Type	Color	Catalog No.
12	LC Duplex	Aqua	FSPNLCDS6AQ
12	LC Duplex	Blue	FSPNLCDS6B
12	LC Duplex	Yellow	FSPNLCDS6Y
6	SC Duplex	Aqua	FSPNSCDS3AQ
6	SC Duplex	Blue	FSPNSCDS3B
24	LC Duplex	Aqua	FSPNLCDS12AQ
6	LC Duplex	Aqua	FSPNLCDS3AQ



Our Most Popular Cassettes

- 100% factory tested and made in the USA
- Premium zirconia ceramic components
- Multimode or singlemode use

Cassettes

Fiber	Ports	Port Configuration	Color	Catalog No.
OM4	24	2 LC Duplex to 2 MPO	Aqua	OCLCD50G4
OM4	24	2 LC Duplex to 2 MPO	Aqua	OCLCQ50G4
OM4	24	2 LC Duplex to 2 MPO	Violet	OCLCD50G4VI
OM4	12	2 LC Duplex to MPO	Aqua	OCLC50G4
OS2	24	2 LC Duplex to 2 MPO	Blue	OCLCDSM



OC Series Splice Cassettes

- Enhanced management of pigtails/fiber slack
- 6, 12, 24-fiber cables or 12-fiber sub-units route into the cassette
- Cleaner install and quicker repairs
- Installation flexibility for small fiber requirements

Splice Cassettes

Adapter Type	Fiber Type	Fiber Strand Count	Adapter Color	Catalog No.
LC	OM3/OM4	12	Aqua	OCSPLCD12M4
		12	Blue	OCSPLCD12S2
	OM3/OM4	6	Aqua	OCSPLCD6M4
		6	Blue	OCSPLCD6S2
	OM3/OM4	24	Aqua	OCSPLCQ24M4
		24	Blue	OCSPLCQ24S2
LC/APC	OS2 SM	6	Green	OCSPLCDA6S2
		12	Green	OCSPLCDA12S2
SC/APC	OS2 SM	6	Green	OCSPSCA6S2
		12	Green	OCSPSCDA12S2
SC	OM3/OM4	12	Aqua	OCSPSCD12M4
		12	Blue	OCSPSCD12S2
	OM3/OM4	6	Aqua	OCSPSCD6M4
		6	Blue	OCSPSCD6S2

Contact your Hubbell representative about our full line of panels and cassettes.