



MARPED30 / MARPED50 INTELLIGENT DOCKSIDE POWER PEDESTALS

Product Features

- Stainless Steel Base and Aluminum Upper Chassis
- Weather resistant repairable paint coating for onsite repairs
- Choose from two 30A outlets, two 50A outlets or a combination of one 30A and one 50A outlet on each side of the pedestal
- One 120V 20A GFCI outlet on each side
- Water spigot variants: ½” to 1 ½”
- Integrated Mesh Wi-Fi with connectivity range up to 600 ft
- Remote management via Dockmaster Console or smartphone app with electrical and water metering
- Segregated electric and water compartments
- Removable top with easy disconnect



**Integrated
Mesh Wi-Fi**



**Software
Management**



**Instant
Alerts**



**Power & Water
Monitoring**



**Easy Relocation &
Storage**



**LED
Lighting**



**Maintenance
Program**



**Best in Class
Durability**

MARPED30 / MARPED50 INTELLIGENT DOCKSIDE POWER PEDESTALS

SPECIFICATIONS

CHARACTERISTICS

Materials	<ul style="list-style-type: none"> • Pedestal base, plate and panels - Stainless Steel 304 • Pedestal body, lightbox, door and panels - Aluminum 5052 • Powder Coat - PolyArmor G17
Dimensions	• 15.75"L x 15.75"W x 55"H
Operating Temperature	• -20C --+60C
Compliances	<ul style="list-style-type: none"> • UL Listed Components,, NEMA 3R, NFPA303, FCC Part 15 • ASTM B117-1985 Salt Spray Corrosive Resistant Tested • NEMA 3R Rain Tested • UV Stabilized F1 Rated Material • Low Voltage Directive • Electromagnetic Directive • UV Stabilized • Flame Retardant
CE	
Typical Weight (AVG)	• 150 lbs.



ELECTRICAL

Outlets	<ul style="list-style-type: none"> • Two 30Amp or 50Amp outlets on each side • One 120V GFCI outlet on each side
Voltage	<ul style="list-style-type: none"> • 30Amp - 120V/250V • 50Amp - 120V/250V
Overload & Fault Current Protection	<ul style="list-style-type: none"> • UL489 Rated Circuit Breakers on each outlet • Additional GFPE breakers on each outlet • Circuit Breaker EN61439-5 and EN IEC 60947-3
Input Voltage	• 120V/240V, 1-Phase 60 HZ 200A
GFCI	<ul style="list-style-type: none"> • 1 per side • 120V 20Amp • In-Use weather-resistant NEMA 3R Cover
Integrated Mesh Wi-Fi	<ul style="list-style-type: none"> • UAP AC Mesh - Dual-Band, 802.11ac Wave 1 Access Point • 500 to 600 ft of extended coverage per pedestal • User and Owner App available for iOS & Android
Safety Features	• Magnetic sensors, if panels open it will auto cut the power

WATER

Taps	1/2"	3/4"	1"	1-1/4"	1-1/2"
Sch 40 Max. Pipe Working Pressure PSI	600	480	450	370	330
Sch 80 Max. Pipe Working Pressure PSI	509	413	378	312	282

LIGHTING

Type	• LED
Color	• 3000K
Battery Backup	• Yes



Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive
• Shelton, CT 06484 • Phone (800) 288-6000 • FAX (800) 255-1031

Printed in U.S.A. Specifications subject to change without notice. ® is a registered trademark of Hubbell Incorporated.

EP_MEP_SF_EN_00135 01/23

