

Features

- Uses the “screensaver” mode of touchscreen HUBBCOMs to display custom graphics
- Ideal for corporate logos, visitor/employee information, or advertising
- Connects to the same Ethernet network as the HUBBCOM™ devices
- Powered by PoE - no separate power supply required
- Simple configuration using a built-in portal website
- UL and CE listed
- Desktop or rack-mounted (with additional hardware)



Touchscreen HUBBCOM™ stations feature....

a “screensaver” mode that blanks the screen when the unit is not in use. The HUBBCOM Media Server, HMS100, allows the blank screensaver to be replaced with customer-supplied images.


The HMS100 provides a simple way to display corporate logos, employee or visitor information, safety instructions, or even advertising messages on HUBBCOM screens.

HMS100 is easily programmed using GAI-TRONICS’ “GUDA” configuration tool and a built-in portal website.

Connectivity

The HMS100 simply connects to the same Ethernet network as the HUBBCOM units.

The unit is powered by Power over Ethernet - no separate power supply is needed.



HUBBCOM™ MEDIA SERVER TECHNICAL SPECIFICATIONS

GENERAL SPECIFICATIONS

Electrical

PoE:

PoE, IEEE 802.23af Class 0: 4.3W/15.4W (idle/maximum)

PoE Plus, IEEE 802.3at Class 4: 4.3W/25.5W (idle/maximum)

Ethernet

Ethernet: 100/1000 Base-T

Speed: 100/1000 Mbps

Cable: Category 5e or better

Connection: RJ-45 T568B jack

Maximum cable length: 100m

Status LEDs: Power

Environmental

Operating temperature range: -4 °F to 131 °F; -20 °C to +55 °C

Relative humidity: 95%

Dimensions

Unit dimensions: 1.72 × 8.50 × 8.91 in

(43.7 H × 215.9 W × 197.9 D mm)

Weight

Unit weight: 5.2 lb: (2.4 kg)

CERTIFICATIONS

CE Mark

NRTL: IEC/UL/CSA 62638-1

ORDER INFORMATION

MODELS	DESCRIPTION
HMS100	HUBBCOM Media Server
12625-001	19" Rack Mount Kit



GAI-TRONICS®



USA Toll Free 1 (800) 492-1212 Tel (610) 777-1374

UK Tel +44 (0)1283 500500

Italy Tel +39 02 48601460

Asia Tel +(65) 6282 2242 (Press 4 for GAI-TRONICS)

Australia Tel 011-61-28-851-5000

Visit Our Website: www.gai-tronics.com

Quality Management System Certified by DNV-GL - ISO 9001:2015. The policy of GAI-TRONICS is one of continuous improvement; therefore the company reserves the right to change specifications without notice.

