

Let Hubbell Be Your Fiber Connection

Fiber Patch Cords

For consistent performance, use FiberHubb™ patch cords in your fiber network. The seamless choice for any fiber interconnect application, these premium cords feature a compact cable size and precision factory termination.

- Reversible polarity high density
- Push/pull options
- Bend-insensitive fiber on all Hubbell patch cords
- OM3, OM4, OS2, OM5, and other custom options available



Standard Duplex available in custom configurations



Uniboot Reversible with or without Push/Pull Tab



Featuring CS & SN Mini-Duplex Designs

FIBERHUBB Series Patch Cords

Description	Cable Color	Length (meters)			
		1m	2m	3m	5m

Standard Duplex

Riser					
LC to LC, OM3	AQ	DFHRCLCLCE1MM	DFHRCLCLCE2MM	DFHRCLCLCE3MM	DFHRCLCLCE5MM
LC to LC, OM4	AQ	DFHRCLCLCF1MM	DFHRCLCLCF2MM	DFHRCLCLCF3MM	DFHRCLCLCF5MM
LC to SC, OM4	AQ	DFHRCLCSCF1MM	DFHRCLCSCF2MM	DFHRCLCSCF3MM	DFHRCLCSCF5MM
LC to LC, OS2	VL	DFHRCLCLCS1SM	DFHRCLCLCS2SM	DFHRCLCLCS3SM	DFHRCLCLCS5SM
LC to SC, OS2	YL	DFHRCLCSCS1SM	DFHRCLCSCS2SM	DFHRCLCSCS3SM	DFHRCLCSCS5SM

Standard lengths shown; custom lengths and colors available.

Plenum					
LC to LC, OM3	AQ	DFHPCLCLCE1MM	DFHPCLCLCE2MM	DFHPCLCLCE3MM	DFHPCLCLCE5MM
LC to LC, OM4	AQ	DFHPCLCLCF1MM	DFHPCLCLCF2MM	DFHPCLCLCF3MM	DFHPCLCLCF5MM
LC to SC, OM4	AQ	DFHPCLCSCF1MM	DFHPCLCSCF2MM	DFHPCLCSCF3MM	DFHPCLCSCF5MM
LC to LC, OM4	VL	DFHPCLCLCF1MVI	DFHPCLCLCF2MVI	DFHPCLCLCF3MVI	DFHPCLCLCF5MVI
LC to LC, OS2	YL	DFHPCLCSCS1SM	DFHPCLCSCS2SM	DFHPCLCSCS3SM	DFHPCLCSCS5SM
LC to SC, OS2	YL	DFHPCLCSCS1SM	DFHPCLCSCS2SM	DFHPCLCSCS3SM	DFHPCLCSCS5SM



FIBERHUBB Series Patch Cords

Description	Cable Color	Length (meters)			
		1m	2m	3m	5m
Reversible High Density					
Reversible Push Pull, Plenum					
LC to LC, Push Pull, OM3/OM4	AQ	HDFHPCLCPRPG4M1	HDFHPCLCPRPG4M2	HDFHPCLCPRPG4M3	HDFHPCLCPRPG4M5
LC to LC, Push Pull, OS2	YL	HDFHPCLCPRPSM1	HDFHPCLCPRPSM2	HDFHPCLCPRPSM3	HDFHPCLCPRPSM5
Reversible Plenum					
LC to LC, OM3/OM4	AQ	HDFHPCLCRPG4M1	HDFHPCLCRPG4M2	HDFHPCLCRPG4M3	HDFHPCLCRPG4M5
LC to LC, OS2	YL	HDFHPCLCRPSM1	HDFHPCLCRPSM2	HDFHPCLCRPSM3	HDFHPCLCRPSM5
Duplex Special					
Plenum					
LCA to LCA, OS2	YL	DFHPCLCALCAS1SM	DFHPCLCALCAS2SM	DFHPCLCALCAS3SM	DFHPCLCALCAS5SM
LCA to SCA, OS2	YL	DFHPCLCASCAS1SM	DFHPCLCASCAS2SM	DFHPCLCASCAS3SM	DFHPCLCASCAS5SM
SCA to SCA, OS2	YL	DFHPCSCASCAS1SM	DFHPCSCASCAS2SM	DFHPCSCASCAS3SM	DFHPCSCASCAS5SM
Riser					
LCA to LCA, OS2	YL	DFHRCLCALCAS1SM	DFHRCLCALCAS2SM	DFHRCLCALCAS3SM	DFHRCLCALCAS5SM
LCA to SCA, OS2	YL	DFHRCLCASCAS1SM	DFHRCLCASCAS2SM	DFHRCLCASCAS3SM	DFHRCLCASCAS5SM
SCA to SCA, OS2	YL	DFHRCSCASCAS1SM	DFHRCSCASCAS2SM	DFHRCSCASCAS3SM	DFHRCSCASCAS5SM
Simplex					
Riser					
LCA to LCA, OS2	YL	SFHRCLCALCAS1SM	SFHRCLCALCAS2SM	SFHRCLCALCAS3SM	SFHRCLCALCAS5SM
LCA to SCA, OS2	YL	SFHRCLCASCAS1SM	SFHRCLCASCAS2SM	SFHRCLCASCAS3SM	SFHRCLCASCAS5SM
LCA to SC, OS2	YL	SFHRCLCASC1SM	SFHRCLCASC2SM	SFHRCLCASC3SM	SFHRCLCASC25SM
LC to LCA, OS2	YL	SFHRCLCLCAS1SM	SFHRCLCLCAS2SM	SFHRCLCLCAS3SM	SFHRCLCLCAS5SM
LC to SCA, OS2	YL	SFHRCLCSCAS1SM	SFHRCLCSCAS2SM	SFHRCLCSCAS3SM	SFHRCLCSCAS5SM
SCA to SCA, OS2	YL	SFHRCSCASCAS1SM	SFHRCSCASCAS2SM	SFHRCSCASCAS3SM	SFHRCSCASCAS5SM
SC to SCA, OS2	YL	SFHRCSCASCAS1SM	SFHRCSCASCAS2SM	SFHRCSCASCAS3SM	SFHRCSCASCAS5SM
SC to SC, OS2	YL	SFHRCSCSCS1SM	SFHRCSCSCS2SM	SFHRCSCSCS3SM	SFHRCSCSCS5SM
CS High Density					
Plenum					
CS to CS, OM3/OM4	AQ	DFHPCCSCSF1MM	DFHPCCSCSF2MM	DFHPCCSCSF3MM	DFHPCCSCSF5MM
CS to CS, OM3/OM4	AQ	DFHPCCSLCF1MM	DFHPCCSLCF2MM	DFHPCCSLCF3MM	DFHPCCSLCF5MM
CS to CS, OS2	YL	DFHPCCSCSS1SM	DFHPCCSCSS2SM	DFHPCCSCSS3SM	DFHPCCSCSS5SM
CS to LC, OS2	YL	DFHPCCSLCS1SM	DFHPCCSLCS2SM	DFHPCCSLCS3SM	DFHPCCSLCS5SM
SN High Density					
Plenum					
SN to LC, OM3/OM4	AQ	DFHPCSNLCF1MM	DFHPCSNLCF2MM	DFHPCSNLCF3MM	DFHPCSNLCF5MM
SN to LC, OS2	YL	DFHPCSNLCS1SM	DFHPCSNLCS2SM	DFHPCSNLCS3SM	DFHPCSNLCS5SM