



- iSTATION System Integration
- Standard Hubbell Keystone Opening
- 3.5mm Stereo Audio (TRS)
- RoHS Compliant

FEATURES

- Easy 110 punch down termination
- Use with mono and stereo audio applications
- Standard 3.5mm stereo jack

SPECIFICATIONS

- Connector:
 - Connector body: brass
 - Nickel plated: 2μ"
 - Type: female to 110 IDC
- Material:
 - Snap Fit connector body: flame retardant high impact thermoplastic
 - Rated UL 94 V-0
- Cable type: Category 5e/6/6A

PERFORMANCE

- Electrical:
 - Distance: 75 feet
- Mechanical:
 - Mating cycles: 500+

STANDARDS

- UL Listed 1863
- RoHS Compliant

HUBBELL iSTATION 110 Termination 3.5mm Stereo Jack



Hubbell's 110 Style Termination 3.5mm Stereo Jack is the perfect solution for distributing audio signal to and from devices. Today's computers and portable electronic devices have standardized on the 3.5mm stereo jack for audio distribution. Having this connection in the plate has become a requirement.

Requiring standard 110 style termination, these connectors install with a "snap" and provide a quick plug in style termination. HPW's 3.5mm Stereo Jacks are available in black only and flush mount into all Hubbell iSTATION plates, modules, frames, surface housings and UDX multimedia panels.

Create a customized multimedia workstation by adding a 110 Style Termination 3.5mm Stereo Jack along with Hubbell's extensive line of AV connectors, loaded modules, Category rated jacks and fiber connectors.

GENERAL INFORMATION

- Important: Always allow for clearance behind connection location to ensure for proper bend radius
- Supplied with IDC termination caps

APPLICATIONS

- Laptop and desktop computers
- Projectors
- Flat panel monitors
- CD, DVD, DVR, MP3, media players
- Gaming devices
- Mobile devices






ORDERING INFORMATION

Hubbell iSTATION 110 Termination 3.5mm Stereo Jack

Unit of Measure	Catalog Number
1 per bag	SF35110BK



DIMENSIONS



ACCESSORIES

USB 2.0 Full Speed 110 Extenders

Description	Color	Catalog Number
Module 1-U	Black	IMU1101BK
	Electric Ivory	IMU1101EI
	Gray	IMU1101GY
	Office White	IMU1101OW
	White	IMU1101W



Hubbell iSTATION Modular Face Plate Frames

	1-Gang	2-Gang
Office White	IMF1xx	IMF2xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



Hubbell iSTATION Keystone Modules

Description	Catalog Number
Keystone, 2-port, flat, 1-unit	IM2K1xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



HDMI 110 Extender Modules

Description	Catalog Number
110 UTP 2-unit HDMI extender (pair)	IMH110ST2xx

xx = Color: **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



Hubbell iSTATION VGA and 3.5mm 110 Extender, 1.5-Unit


Color	Catalog Number
Black	IM15311015BK
Electric Ivory	IM15311015EI
Gray	IM15311015GY
Office White	IM15311015OW
White	IM15311015W



INSTALLATION TIPS

Termination: Station cable side of connection is a 110 style punch down. Simply lace in pair 1 and pair 2 from left to right on the IDC block. For example pair 1 (the blue pair) use the (pin 3) blue conductor and then (pin 1) blue/white, (pin 2) orange, (pin 4) orange/white. The key practice is to use the same pair/pairs on each side of the horizontal run.

Important: Use the same pair color combinations for each application (composite, component, left and right audio, 3.5mm and S-video).



- 3 Blue
- 2 Orange
- 1 Blue/White
- 4 Orange/White