



- 3A of 5V DC Power in a Compact In-Wall Duplex Outlet
- Integrated 5V DC Rear Flying Leads to Power AV Devices
- Device Charging and Powering AV Modules
- RoHS compliant

FEATURES

- Integrated, switchable 3A, 5V DC power supply
- One USB charging port, Type A
- Tamper-resistant (TR) decorator duplex
- Green LED indicator shows if 5V power available
- Back and side wire for solid or stranded wire
- Flush fit design
- Terminal covers

SPECIFICATIONS

- Electrical ratings: 15A, 125V AC
- Input voltage: 125V AC, 60Hz
- Output voltage: 3A, 5V DC
- Circuit feed-through 20A, 125V
- #10-14 AWG gauge wire terminals
- Dielectric withstand: 2000V
- Operating temperature: maximum continuous 75°C; minimum -40°C (without impact)
- Meets UL94 for 5V flammability rating
- Complies with battery charging specification USB BC1.2
- USB port rated for a minimum 10,000 insertions
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products
- Complies with Part 15 of the FCC rules
- cULus listed to UL498 and UL1310

HUBBELL iSTATION Tamper-Resistant Receptacle with 5V DC Power Output



Hubbell's **USB Charger Receptacle** with auxiliary 5V DC output provides USB charging, DC power and AC power in a standard single gang electrical opening. Designed to provide DC power to support active AV components by eliminating the need for external power supplies, it also provides a high speed USB charging port for charging personal electronics. A DC power supply switch is provided to turn off DC power for servicing and troubleshooting. The tamper-resistant Style Line® decorator AC outlets provide additional power for AV components and displays.

APPLICATIONS

Ideal for use in renovation, new construction and to add capacity for USB charging and supplying power to active AV components. Especially suited for use in universities, hotels, hospitals, restaurants, airports, classrooms and homes.

Designed for use with:

- Hubbell active AV modules
- Tablet computers
- Apple® products
 - iPad®
 - iPod® smart phones
 - iPhone® mobile phones
- GPS
- Smart phones
- Mobile phones
- Other USB compatible products
- Digital readers

Apple, iPad, iPod and iPhone are registered trademarks of Apple, Inc.



ORDERING INFORMATION

Tamper-Resistant Receptacle with 5V DC Power Output

Description	Input Voltage	Output Voltage	Catalog No.
USB Charger Tamper-Resistant Receptacle, (1) USB Port 3A, 5V DC output, 15A, 125V AC Decorator Duplex	125V AC	5V DC	AVPS15xx



xx = Color: **BK** (Black), **I** (Ivory), **GY** (Gray), **OW** (Office White), or **W** (White). Light Almond is the same color as Office White.

ACCESSORIES

HDBase-T Frames and Modules

Description	Installation	Style Line® Frame	3-Unit Module
110 HDBase-T HDMI, USB, RS232, IR extender (pair), 5V DC	Single 4-pair UTP Cable	ISFHDBT3xx	IMHDBT3xx



xx = Color: **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), or **W** (White). Light Almond is the same color as Office White.

HDMI High-Definition 110 UTP Video Extender

Description	DC	Installation	2-Unit Module
110 UTP HDMI extender (pair)	5 Volt	(2) 4-pair UTP Cables	IMH110ST2xx



xx = Color: **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), or **W** (White). Light Almond is the same color as Office White.

Two-Gang Large Capacity Wall Box - 66.7 Cubic Inch Capacity

Description	Dimensions	Knockouts Sides*	Knockouts Back*	Catalog No.
Square 2-gang wall box	4 ^{11/16} "H x 4 ^{11/16} "W x 3 ^{1/4} "D	(2) 3/4" - 1" TKO; (2) 1" - 1 1/4" TKO; (2) 1" - 2" conc. KO	(2) 3/4" - 1" TKO (2) 1/2" TKO	HBL260

*TKO (Tangential Knockout)

Note: Use with industry standard 4^{11/16}" square mud rings for 1- or 2-gang applications.

Three-Gang Large Capacity Wall Box - 113.3 Cubic Inch Capacity

Description	Dimensions	Knockouts Sides	Knockouts Back	Catalog No.
Square 2- or 3-gang wall box	4 ^{11/16} "H x 7 ^{3/4} "W x 3 ^{1/4} "D	(4) 1/2" - 3/4" TKO, (4) 3/4" - 1" TKO, (2) 1" - 1 1/4" TKO, (2) 1" - 2" conc. KO	(2) 1/2" - 3/4" TKO, (2) 3/4" - 1" TKO, (2) 1" - 1 1/4" TKO	HBL263

Note: Use with industry standard 4" square mudrings for 1- or 2-gang applications.

3-Gang Mud Rings - Compatible with HBL263

Height	Capacity (cu. in.)	Catalog No.
1/2"	10.1	HBL792
5/8"	12.3	HBL793
1 1/4"	24.3	HBL794

Low Voltage Partition

Compatible with	Compatible Mud Ring Depth	Packing Quantity	Catalog No.
HBL260 and HBL263	1/2", 3/4" and 1 1/4"	1	HBL981AVD

DIMENSIONS

Note: For use with boxes deeper than 1.5" with internal AC/MC clamps.

