



# HUBBELL® Premise Wiring

## CABLE MANAGEMENT

### A M SERIES VERTICAL CABLE MANAGERS

Available Widths	Front Depth	Rear Depth	Catalog No.
6", 8", 10", 12"	10"	-	<b>VMx10</b>
		3"	<b>VMx13</b>
		8"	<b>VMx18</b>
		10"	<b>VMx20</b>

x = Width: 6, 8, 10 or 12"

### B M SERIES HORIZONTAL CABLE MANAGERS

Available Heights (RU)	Front Depth	Rear Depth	Cover	Catalog No.
1, 2, 3, 4	4"	-	Included	<b>HMx4C</b>
	7"	-	Included	<b>HMx7C</b>
	7"	7"	Included	<b>HMx77C</b>
	4"	-	-	<b>HMx4</b>

x = Height: 1, 2, 3 or 4 RU

### C S SERIES VERTICAL CABLE MANAGERS

Width	Front Depth	Rear Depth	Full Kit	Catalog No.
4"	6"	3"	-	<b>VS74x</b>
6"	6"	3"	-	<b>VS76x</b>
6"	6"	3"	2 verticals + relay rack	<b>CS1976x</b>

x = Add H to end of Catalog Number for Hinged Cover

### D S SERIES HORIZONTAL CABLE MANAGERS

Available Heights (RU)	Front Depth	Cover	Catalog No.
1, 2	3"	-	<b>HSx3</b>
		Included	<b>HSx3C</b>


x = Height: 1 or 2 RU

### E SD SERIES CABLE MANAGERS

Type	Depth	Dimension	Catalog No.
Vertical	4"	5" width	<b>VSD45</b>
Horizontal	3"	1 RU	<b>HSD13</b>
Horizontal	3"	2 RU	<b>HSD23</b>

### CABLE MANAGEMENT SPOOLS

Type	Quantity	Depth	Catalog No.
Spool	50	3"	<b>ICKS5</b>
		6"	<b>ICKS56</b>
		9"	<b>ICKS59</b>



M Series Cable Manager

S Series Cable Manager

SD Series Cable Manager

Relay Rack

iFRAME Cable Management

Full Size Enclosure

QUADCAB® Wall Mount Cabinet

RE-BOX® Cabinet

## MOUNTED CABINETS

### A CONSOLIDATION POINT ENCLOSURES

Dimensions	Color	Catalog No.
21"x14.5"x4.5"	Ivory	<b>CPE1</b>
	Black	<b>CPEB</b>

### B RE-BOX® 100LB CAPACITY CABINET

Maximum Switch Depth	Rack Units	Catalog No.
14"	2	<b>RE2x</b>
	5	<b>RE4x</b>
22"	5	<b>RE4Xx</b>

x = Color: Light Gray is standard, add B for Black

### ZONE BOXES

Description	Rack Units	Catalog No.
Raised floor mount	4	<b>ZAFB4U6</b>
	8	<b>ZAFB8U8</b>
Ceiling mount	5	<b>ZCB5UP</b>
	7	<b>ZCB7UA</b>

### E CEILING ENCLOSURES

Description	Catalog No.
White	<b>AVCE1</b>
Plenum Rated, White	<b>AVCE1P</b>
Data kit included	<b>AVCE1KIT</b>
Wireless Access Point	<b>WBC1</b>
Cisco® Aironet® 1200	<b>WBC12</b>

### F QUADCAB®, 400LB CAPACITY WALL MOUNT CABINETS

Available Depths	Rack Units	Door Style	Catalog No.
20", 26", 36"	12	Window	<b>HSQ24xx</b>
		Solid	<b>HSQ24Sxx</b>
19	19	Window	<b>HSQ36xx</b>
		Solid	<b>HSQ36Sxx</b>
26	26	Window	<b>HSQ48xx</b>
		Solid	<b>HSQ48Sxx</b>

xx = Depth: 20" is standard, add 26 for 26", 36 for 36"

### G WALL MOUNT BRACKET, BOTTOM HINGE

Available Depths	Rack Units	Catalog No.
4"	1	<b>HPWWB1Ux</b>
4", 8"	2	<b>HPWWB2Ux</b>
4", 8"	4	<b>HPWWB4Ux</b>
4", 8", 18"	8	<b>HPWWB6Ux</b>

x = Depth: 4, 8 or 18" as available

### WALL MOUNT BRACKET, SIDE HINGE

Available Depths	Height	Catalog No.
4", 8"	1U	<b>BRMCCMB19X35Xx</b>
	2U	<b>BRMCCMB19X7Xx</b>

x = Depth: 4 or 8"

### H WALL MOUNT SWING FRAME

Available Heights	Rack Units	Catalog No.
24", 36", 48"	12, 19, 26	<b>HPWWMRxx</b>

xx = Height: 24, 36 or 48"

### I RE-BOX® INDUSTRIAL ENCLOSURE, NEMA RATED

Available Heights	NEMA	Catalog No.
24", 36", 48"	4R	<b>IRxUG</b>
24", 36"	4X	<b>IRxUSS</b>

x = Height: Insert 2 for 24", 3 for 36" or 4 for 48"

Cisco® and Aironet® are registered trademarks of Cisco Systems, Inc.

