

Smart Design for Your Home



Hubbell tradeSELECT® and netSELECT® Products for Your Home

Select the best when it comes to electrical devices and voice/data products. Choose Hubbell for the superior performance, innovation and style that your home deserves.



Styling for Looks and Safety



When you think safety, think Hubbell. Our range of products makes a difference. GFCI and AFCI receptacles provide the best in people and fire protection, minimizing worry about shocks and electrical fires. Tamper-resistant receptacles reduce the risk of injury by preventing foreign objects from making electrical contact. New nightlight switches and receptacles provide a guiding light without using too much energy. But putting safety first doesn't mean that aesthetics should be ignored. To align with residential décor, Hubbell wiring devices are offered in a full range of designs that blend beautifully with furnishings and finishes.

Energy Savings Like Never Before

Energy efficiency isn't just good for the environment – it's good for homeowners, too. Occupancy sensors and timers offer real energy savings so you can enjoy significant long-term, ongoing reductions in electric bills. Hubbell offers a range of options for controlling residential energy use. Sensors turn



lights on when you need them, and automatically turn them off when you leave the room. Digital timers provide economic lighting and fan control with just the touch of a finger. LED-compatible dimmers allow you

to control lighting levels, offering just the right atmosphere with comfort and convenience.



Technology and the Interconnected World



To accommodate advanced electronic devices, homes need to be wired for the ever-changing pace of technology. Not only should wiring systems complement aesthetics, but they should also be efficient, reliable, and safe in order to support computers, televisions, and security systems. From network enclosures to USB charging stations, Hubbell has a broad line of products that are specifically designed to support the connectivity and power needs of homeowners.



Safety



Nightlight Decorator Switches

Description	Single Pole 20A, 120/277
Ivory Light Almond White	DS120NLIV DS120NLLA DS120NLWH



Nightlight Receptacle

Description	15A 125V
Ivory Light Almond White	DR15NLIV DR15NLLA DR15NLWH



Nightlight Only

Description	120V
Ivory Light Almond White	DD100NLIV DD100NLLA DD100NLWH



GFCI Receptacles

Weather and Tamper-Resistant

Description	15A 125V	20A 125V
Ivory Light Almond White	GFTWRST15I GFTWRST15LA GFTWRST15W	GFTWRST20I GFTWRST20LA GFTWRST20W



ARC Fault Receptacles

with Tamper-Resistant Outlets

Description	15A 125V	20A 125V
Ivory Light Almond White	AFR15TRI AFR15TRLA AFR15TRW	AFR20TRI AFR20TRLA AFR20TRW



Tamper-Resistant Receptacles

15A 125V

Description	Decorator	Duplex
Ivory Light Almond White	RRD15SITR RRD15SLATR RRD15SWTR	RR15SITR RR15SLATR RR15SWTR

Energy Management



Passive Infrared Wall Switches

Manual/Auto On, 3-Way Capable

Description	Standard	with Neutral
Ivory Light Almond White	WS2000I WS2000LA WS2000W	WS2004I — WS2004W



Passive Infrared Wall Switches w/ Nightlight

Manual/Auto On, 3-Way Capable

Description	Standard	with Neutral
Ivory Light Almond White	WS2000NI WS2000NLA WS2000NW	WS2004NI — WS2004NW



Count Down Timer Wall Switch

1000W@120V AC and 1400W @ 277V AC

Description	Catalog Number
30 Min. (Off, 5, 10, 20, 30) 60 Min. (Off, 15, 30, 45, 60) 12 Hrs. (Off, 2, 4, 8, 12)	DT5030xx DT5060xx DT5012xx

xx = Color. Replace w/ **I** (Ivory), **LA** (Lt. Almond) or **W** (White).

Connectivity/Technology



USB Charging Receptacle

Tamper-Resistant Receptacle, two USB type 2.0 ports, 3.8 Amp, 5 Volt DC

Description	15A 125V	20A 125V
Ivory Light Almond White	USB15X2I USB15X2LA USB15X2W	USB20X2I USB20X2LA USB20X2W



USB Charger 4 Port Outlet

Four USB Type 2.0 Ports, 5 Amp, 5 Volt DC

Description	USB Outlet	Surge Receptacle
Ivory Light Almond White	USB4I USB4LA USB4W	HBL5260ISA — HBL5260WSA

*Charging station shown consists of Surge Receptacle **HBL5260WSA**, Wallplate **NP262W** and 4 Port USB **USB4W**



Network Enclosure

Pre-Configured Network System

Description	Catalog Number
Basic home network kit includes: (1) box w/ hinged cover, (1) primary 8-port tele. module, (1) 4-way coaxial splitter module	NSOBNK14
Enclosure only	10 Inch 14 Inch 28 Inch
	NSOBX10 NSOBOX14 NSOBOX28

Floor Boxes

Recessed GFCI/Decorator Opening 4 Inch Minimum Concrete Pour



Gray PVC Floor Box	Cover Assembly	
	Material/Color	Catalog Number
RF400	Solid Brass Black Aluminum	RF406BR RF406BK RF406ALU

Under Cabinet/Counter Boxes

Complies with NEC for Kitchen Receptacles



Cover	Slim Box	GFCI Fit Box
Stainless Steel White Metal White Nylon	RU100SS RU100W RU170W	RU200SS RU200W RU270W

Flat Panel TV Boxes In Wall Delivery

Allows Flat Panel Displays to Sit Flush against Wall



Description	Catalog Number
2-Gang Enclosure Cover with Cable Exit Standard Power Kit	NSAV62M NSAV6C NSOKPTR

Please see the tradeSELECT® and netSELECT® sections of the full line Hubbell Catalog for complete product offering.