



CHANCE® INSTANT FOUNDATION SOLUTIONS

ROADWAY | DECORATIVE | AREA/SITE LIGHTING



CHANCE® Instant Foundations are a pre-engineered anchor method for decorative or architectural, roadway/DOT, or area/parking lighting. Specifically designed for above-grade and at-grade mounting, these extendable foundation anchors have high-strength shafts to resist bending moments.

KEY BENEFITS:

- Immediate loading - no wait for concrete to cure
- Remove and reuse the foundation. Simply reverse the motor to back out.
- Designed and engineered in the USA - Centralia, MO
- Quick and easy installation using standard hydraulic equipment
- Installs in most weather conditions, even below freezing
- No excavation or spoil removal
- Commonly installed in 10 minutes with a two-man crew

QUICK AND EASY INSTALLATION



CHANCE foundations are commonly installed in 10 minutes with a two-man crew.



Variable bolt circle styles allow for fast bolt-up as the slotted design mates with most light standards.



One-trip convenience cuts cost and saves time.

Pre-cut cableway in the pipe shaft provides quick wiring

Since no concrete is used, the standard can be loaded immediately.

Welded spiral plate (a true helix) acts as a screw during installation and a load-bearing member in place.



CHANCE® The Certified Helical Pile™

CHANCE Civil Construction | 210 North Allen Street | Centralia, MO 65240 | United States of America
©Copyright 2019 Hubbell Incorporated. Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.
Printed in the U.S.A. | SF_04_248_E_0819

