

EASY-ON CUTOUT ARRESTER BRACKET

FOR EFFORTLESS INSTALLATION

APPLICATION


- Bracket for mounting single cutout, arrester, cable terminator and cutout-arrester combinations to crossarm

FEATURES


- Direct correlation to NEMA styles
- Fully assembled and ready to install
- Easy-On feature allows for installation with gloves
- Captive bolts

MATERIAL

- Steel, Galvanized per ASTM A-153



NEMA B Bracket



NEMA B Extended Bracket



NEMA A Bracket



Cutout-Arrester
Combination Bracket

Hubbell SKU	Bracket Type	Range of Crossarm Widths	Range of Crossarm Heights	Crossarm Bolt Size	Extension (Face of Arm to Center of Mounting Bolt)	Mounting Bolt Size	Bracket Material Size	Approx. Ship Wt. per Each
PSC2060980	NEMA B	3-1/2" to 6"	4-1/8" to 5-3/8"	3/8" x 8"	2-1/4"	1/2" x 2"	3/8" x 1-3/4"	4.22 lbs.
PSC2061042	NEMA B	3-1/2" to 6"	4-1/8" to 5-3/8"	3/8" x 8"	2-1/4"	1/2" x 1-1/2"	3/8" x 1-3/4"	4.14 lbs.
PSC2061043	NEMA B	2-3/4" to 4"	4-1/8" to 5-3/8"	3/8" x 6"	2-1/4"	1/2" x 2"	3/8" x 1-3/4"	4.16 lbs.
PSC2061044	NEMA B	2-3/4" to 4"	4-1/8" to 5-3/8"	3/8" x 6"	2-1/4"	1/2" x 1-1/2"	3/8" x 1-3/4"	3.90 lbs.
C2060280EZ	Extended NEMA B	2-3/4" to 4"	4-1/8" to 5-1/8"	3/8" x 5"	5"	1/2" x 2"	3/8" x 2"	3.70 lbs.
C2060127EZ	NEMA A	2-3/4" to 4"	4-1/8" to 5-1/8"	3/8" x 5"	2-1/2"	1/2" x 1-1/2"	5/16" x 1-1/2"	2.30 lbs.
C2060632EZ	Cutout-Arrester Combo	2-3/4" to 4"	4-1/8" to 5-1/8"	3/8" x 5"	2-3/4"	3/8" x 1-1/2" & 3/8" x 2"	3/8" x 2"	3.75 lbs.

