


# CROSSARM LINK STICK



## NEW LIVE-LINE SOLUTION FOR DEADEND APPLICATIONS

### QUICKLY PUTS INSULATED LINK IN HOIST-ASSISTED JOBS:

- 1-1/4"-diameter Epoxiglas<sup>®</sup> pole with 21-1/2" insulating length
- 1,500lb.-rated working load
- Platisol-coated 3/4"-diameter steel hook
- Hook's 5" opening fits standard 3-3/4" x 4-3/4" crossarms
- Galvanized-steel swivel eye on pole end for easy alignment
- Lifting eye on hook fitting for positioning by a hot line tool



Catalog No. PSC4004132

SF09024E

*Hubbell has a policy of continuous product improvement. Please visit [hubbellpowersystems.com](http://hubbellpowersystems.com) to confirm current design specifications.*