

6H BALL SOCKET CLAMPS FOR 35MM BALL STUD



FEATURES AND BENEFITS

- 6H-Rated 35mm Ball Socket Clamps with bronze body
- Eye-Screw or T-Handle options available; both with threaded ferrule holes
- Bronze Eye Screw/T-Handle - 5/8-11UNC
- Tested per ASTM F855-20 to Grade 6H (55kA; 148kA 1st cycle peak; X/R=30)
- Connects to PSC6003581 35mm Ball Stud
- PSS18102 SafetyFlex™ 4/0+ Cable (2318 strands) must be used to achieve 6H rating for the ground set
- Available with factory-assembled sets (recommended) or as an individual component

Catalog Number	Description	Weight
PSC6003711	6H 35mm Ball Socket Clamps with Eye-Screw	2.1 lbs. (0.94 kg)
PSC6003713	6H 35mm Ball Socket Clamps with T-Handle	2.1 lbs. (0.94 kg)
PSC6003581	35mm Ball Stud	1.4 lbs. (0.64 kg)
PSS18102	SafetyFlex™ 4/0+ Cable (2318 strands)	0.87 lb/ft (1.3 kg/m)

CONTACT YOUR LOCAL HPS REPRESENTATIVE FOR CUSTOM LENGTH GROUNDING SETS



CHANCE
LINEMAN GRADE TOOLS

hubbellpowersystems.com

For product inquiries, please contact your local sales representative or customer service representative.

©2021 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.
Printed in the U.S.A. | SF_09_222E