

TURNER BEARTRAP™ 2-WAY SWITCHES

TU-2TS2 ALUMINUM 2-WAY SIDE BREAK SWITCHES RATINGS 38-170kV AND 600-2000A

KEY BENEFITS

- Speed Independent operation—can be closed either fast or slow
- Reverse-loop, silver-plated copper jaw contacts—employ the natural repulsion of magnetic fields moving in opposite directions to exert holding forces against the blade edges
- Anti-Rollover Device—the BearTrap Switch from Turner employs a patented ramp and pin to securely position the blade in the jaw.
- Blade Position Indicator—High visibility stickers provide positive indication of the switch being open or closed. They also have high UV protection and come standard on every switch.
- Switching—allows for 2-way switching, swapping between sources for a load

