

# TURNER BEARTRAP™ 1-WAY SWITCHES

## **TU-1AS2 ALUMINUM 1-WAY SIDE BREAK SWITCHES RATINGS 38-170kV AND 600-2000A**

### **KEY BENEFITS**

- Speed Independent operation—can be closed either fast or slow
- Reverse-loop, silver-plated copper jaw contacts—employ the natural repulsion of magnetic fields moving in opposite directions to exert holding forces against the blade edges
- Anti-Rollover Device—the BearTrap Switch from Turner employs a patented ramp and pin to securely position the blade in the jaw
- Blade Position Indicator—High visibility stickers provide positive indication of the switch being open or closed. They also have high UV protection and come standard on every switch.
- Switching—offered in two, three, and four way mounting configurations for inline or 90-degree takeoffs

