



#	Switch type	Operator	Bushing Creep Distance	Load Rating	Product Description	kV L-G	kV BIL	Spec #	Description	Alt Supply options		Part # ^{1,2}
										240Vac	125Vdc	

UltraVac Vacuum Solid Dielectric Switch (Motor Operated)

1	Solid Dielectric	Motor Operator	27"	200A	UltraVac15-110	15	110	N/A	33247501, Trinetics, UltraVac15-110, 15kV, 110kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33247501
2	Solid Dielectric	Motor Operator	27"	200A	UltraVac15-125	15	125	N/A	33249401, Trinetics, UltraVac15-125, 15kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33249401
3	Solid Dielectric	Motor Operator	33"	200A	UltraVac20-125	20	125	N/A	33247601, Trinetics, UltraVac20-125, 20kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33247601
4	Solid Dielectric	Motor Operator	33"	200A	UltraVac20-150	20	150	N/A	33248401, Trinetics, UltraVac20-150, 20kV, 150kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33248401

Compact UltraVac Vacuum Solid Dielectric Switch (Motor Operated)

5	Solid Dielectric	Motor Operator	11.5"	200A	Compact UltraVac15-110	15	110	Compact	33247501C, Trinetics, Compact UltraVac15-110, 15kV, 110kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33247501C
6	Solid Dielectric	Motor Operator	11.5"	200A	Compact UltraVac15-125	15	125	Compact	33249401C, Trinetics, Compact UltraVac15-125, 15kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33249401C
7	Solid Dielectric	Motor Operator	18"	200A	Compact UltraVac20-125	20	125	Compact	33247601C, Trinetics, Compact UltraVac20-125, 20kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33247601C
8	Solid Dielectric	Motor Operator	18"	200A	Compact UltraVac20-150	20	150	Compact	33248401C, Trinetics, Compact UltraVac20-150, 20kV, 150kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33248401C

UltraVac Vacuum Solid Dielectric Switch (Solenoid Operated)

9	Solid Dielectric	Solenoid Operator	33"	200A	UltraVac15-110	15	110	N/A	33247102, Trinetics, UltraVac15-110, 15kV, 110kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33247102
10	Solid Dielectric	Solenoid Operator	33"	200A	UltraVac24-125	24	125	N/A	33247202, Trinetics, UltraVac24-125, 24kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33247202
11	Solid Dielectric	Solenoid Operator	33"	200A	UltraVac24-150	24	150	N/A	33247402, Trinetics, UltraVac24-150, 24kV, 150kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33247402

Compact UltraVac Vacuum Solid Dielectric Switch (Solenoid Operated)

12	Solid Dielectric	Solenoid Operator	18"	200A	Compact UltraVac15-110	15	110	Compact	33247102C, Trinetics, Compact UltraVac15-110, 15kV, 110kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33247102C
13	Solid Dielectric	Solenoid Operator	18"	200A	Compact UltraVac24-125	24	125	Compact	33247202C, Trinetics, Compact UltraVac24-125, 24kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33247202C
14	Solid Dielectric	Solenoid Operator	18"	200A	Compact UltraVac24-150	24	150	Compact	33247402C, Trinetics, Compact UltraVac24-150, 24kV, 150kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33247402C
15	Solid Dielectric	Solenoid Operator	18"	400A	Compact UltraVac15-110	15	110	Compact	33257102C, Trinetics, Compact UltraVac15-110, 15kV, 110kV BIL, 400A vacuum switch in solid dielectric insulation, with 2-hole terminal pads, manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33257102C
16	Solid Dielectric	Solenoid Operator	18"	400A	Compact UltraVac22-125	22	125	Compact	33257202C, Trinetics, Compact UltraVac22-125, 22kV, 125kV BIL, 400A vacuum switch in solid dielectric insulation, with 2-hole terminal pads, manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33257202C
17	Solid Dielectric	Solenoid Operator	18"	400A	Compact UltraVac22-150	22	150	Compact	33257402C, Trinetics, Compact UltraVac22-150, 22kV, 150kV BIL, 400A vacuum switch in solid dielectric insulation, with 2-hole terminal pads, manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	y	33257402C

CSD Oil Switch

24	Oil	Motor Operator	11"	200A	CSD15-95	15	95	6610	33050001, Trinetics, CSD15-95, 15kV, 95kV BIL, 200A oil switch, with 11" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33050001
25	Oil	Motor Operator	17"	200A	CSD15-125	15	125	6770	33078601, Trinetics, CSD15-125, 15kV, 125kV BIL, 200A oil switch, with 17" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33078601

#	Switch type	Operator	Bushing Creep Distance	Load Rating	Product Description	kV L-G	kV BIL	Spec #	Description	Alt Supply options		Part # ^{1,2}
										240Vac	125Vdc	
26	Oil	Motor Operator	17"	90A	CSD20-125	20	125	6842	33184601, Trinetics, CSD20-125, 20kV, 125kV BIL, 90A oil switch, with 17" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33184601
27	Oil	Motor Operator	24"	90A	CSD20-150	15	150	6843	33184701, Trinetics, CSD20-150, 20kV, 150kV BIL, 90A oil switch, with 24" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33184701

VS Vacuum Under Oil Switch

28	Vacuum Under Oil	Motor Operator	11"	200A	VS15-95	15	95	6814	33184401, Trinetics, VS15-95, 15kV, 95kV BIL, 200A vacuum under oil switch, with 11" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33184401
29	Vacuum Under Oil	Motor Operator	17"	200A	VS15-125	15	125	6815	33183501, Trinetics, VS15-125, 15kV, 125kV BIL, 200A vacuum under oil switch, with 17" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33183501
30	Vacuum Under Oil	Motor Operator	17"	200A	VS24-125	24	125	6869	33195601, Trinetics, VS24-125, 24kV, 125kV BIL, 200A vacuum under oil switch, with 17" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33195601
31	Vacuum Under Oil	Motor Operator	17"	200A	VS24-150	24	150	6870	33195701, Trinetics, VS24-150, 24kV, 150kV BIL, 200A vacuum under oil switch, with 17" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33195701
32	Vacuum Under Oil	Motor Operator	24"	200A	VS24-150	24	150	6871	33195801, Trinetics, VS24-150, 24kV, 150kV BIL, 200A vacuum under oil switch, with 24" creep bushings, manual handle, 120V motor operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards.	y	n	33195801

UltraVacLT Vacuum Solid Dielectric Switch

33	Solid Dielectric	Solenoid Operator	25"	200A	UltraVacLT15-95	15	95	N/A	ULT15-095B1W5SE1XX, Trinetics, UltraVacLT, 15kV, 95kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards. Ultra compact and light weight (20lbs).	y	y	ULT15-095B1W5SE1XX
34	Solid Dielectric	Solenoid Operator	25"	200A	UltraVacLT15-110/125	15	110	N/A	ULT15-125B1W5SE1XX, Trinetics, UltraVacLT, 15kV, 110/125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards. Ultra compact and light weight (20lbs).	y	y	ULT15-125B1W5SE1XX
35	Solid Dielectric	Solenoid Operator	25"	200A	UltraVacLT27-125	27	125	N/A	ULT27-125B1W5SE1XX, Trinetics, UltraVacLT, 27kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards. Ultra compact and light weight (22lbs).	y	y	ULT27-125B1W5SE1XX
36	Solid Dielectric	Solenoid Operator	25"	200A	UltraVacLT27-150	27	150	N/A	ULT27-150B1W5SE1XX, Trinetics, UltraVacLT, 27kV, 125kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards. Ultra compact and light weight (22lbs).	y	y	ULT27-150B1W5SE1XX

SmartClose Synchronous Vacuum Capacitor Switch

37	Solid Dielectric	Solenoid Operator	18"	200A	3 Phase SmartClose15-110	15	110	Compact	SMC15-110D1D2ME6XX, SmartClose15-110, 15kV, 110kV BIL, 200A 3ph tank capacitor switch with 3-120V solenoid operators for optional independent pole operation, 3 manual open/close handles, 6 integral voltage sensors, substation frame compatible mounting flange, 5-pin receptacle for control cable, and fiber optic compartment with 2 AVAGO snap-on bulkhead connectors. Includes wildlife covers.	n	n	SMC15-110D1D2ME6XX
38	Solid Dielectric	Solenoid Operator	18"	400A	3 Phase SmartClose15-110	15	110	Compact	SMC15-110E1D2ME6XX, SmartClose15-110, 15kV, 110kV BIL, 400A 3ph tank capacitor switch with 3-120V solenoid operators for optional independent pole operation, 3 manual open/close handles, 6 integral voltage sensors, substation frame compatible mounting flange, 5-pin receptacle for control cable, and fiber optic compartment with 2 AVAGO snap-on bulkhead connectors. Includes wildlife covers.	n	n	SMC15-110E1D2ME6XX
39	Solid Dielectric	Solenoid Operator	18"	200A	3 Phase SmartClose27-125	27	125	Compact	SMC27-125D1D2ME6XX, SmartClose27-125, 27kV, 125kV BIL, 200A 3ph tank capacitor switch with 3-120V solenoid operators for optional independent pole operation, 3 manual open/close handles, 6 integral voltage sensors, substation frame compatible mounting flange, 5-pin receptacle for control cable, and fiber optic compartment with 2 AVAGO snap-on bulkhead connectors. Includes wildlife covers.	n	n	SMC27-125D1D2ME6XX
40	Solid Dielectric	Solenoid Operator	18"	400A	3 Phase SmartClose27-125	27	125	Compact	SMC27-125E1D2ME6XX, SmartClose27-125, 27kV, 125kV BIL, 400A 3ph tank capacitor switch with 3-120V solenoid operators for optional independent pole operation, 3 manual open/close handles, 6 integral voltage sensors, substation frame compatible mounting flange, 5-pin receptacle for control cable, and fiber optic compartment with 2 AVAGO snap-on bulkhead connectors. Includes wildlife covers.	n	n	SMC27-125E1D2ME6XX

NOTES:

- 1 All motor operated switches standard with "01" suffix include no auxiliary contacts
- 2 All solenoid switches standard with "02" suffix include Form C aux switch with AC common neutral. SmartClose excluded.