
# Work Surface Connectivity Boxes





Delivering Power and Data to the Work Surface



# Furniture and Work Surface Connectivity Boxes

This family of furniture and work surface connectivity boxes installs into conference tables and workstations to bring power, voice, data, and multimedia directly to the point of use. In addition, they offer an aesthetic design with improved cable management. Now, users can plug in laptops, projectors and other equipment at the desktop level - no more crawling under the table or moving obstacles to get to the electrical outlet and network connectivity.



# **Furniture and Work Surface Connectivity Boxes**



Flush Mount Boxes

Hubbell offers square and rectangular flush mount boxes in a variety of configurations. These boxes are available in stainless steel, anodized aluminum or painted finishes to match any décor. Boxes are designed for easy installation and are available pre-wired or empty for field wiring.



Lift-up Style Boxes

Offering a convenient and attractive method for work surface power and data connections, these boxes are available in several finishes. When not in use, services are concealed by flipping the unit down.



**2X2 USB Work Surface Pop-Up Box** Simple push-down method for opening and closing, two 125V receptacles plus two USB charging ports, 3 Amps of USB charging, with minimal 5 inch square footprint, pre-wired 5 foot cord, NEMA 5-15P plug. Available in brushed aluminum or black powder coat finishes.

# **Table Top Boxes**



**Pre-Wired Boxes** 

Round dual-service boxes easily install into a 3½-inch diameter core hole. Power is pre-wired and keystone openings accommodate data or multi-media activation.



**Pre-Wired Boxes** Configured with 15A power outlet, 15-pin feed through and 3.5mm audio jack. This unit allows for further customization by populating two keystone openings.



Low Voltage Boxes

Low voltage only units are available pre-loaded with XLR microphone jack or with keystone opening for Hubbell snap-fit modules.



Multiple finish options to match any style or décor. All models in the Work Surface Series are pre-wired for easy installation.



#### 2X2 USB Work Surface Pop-Up Box

Description	Surface Dimensions	Cut out dimensions	Product Depth	Max. Surface Thickness	Finish	Catalog Number
15A duplex receptacle with (2) USB charging ports, 3A USB charging capacity with pre-wired with 5 ft. electrical cord	5" x 5"	4.62" x 4.62"	3.55"	1.125"	Brushed Aluminum Black Powder Coat	WSBUSB2X2ALU WSBUSB2X2BLK

#### Square Lift-Up Style

Description	Finish	Dimensions	Catalog Number
Two (2) pre-wired 15A outlets with 6-ft. power supply cord; 1-Unit opening for Hubbell iSTATION modules.	Black Silver	5.75"L x 5.39"W x 4.25"H	WSBC21UBK WSBC21USV
Unit rotates up when in use and down to conceal	Silver		W3BC2103V
services when not in use			

#### Square Mini Lift-Up Style

Description	Finish	Dimensions	Catalog Number
One (1) pre-wired 15A outlet with 9-ft. power supply cord; One (1) RJ-45 jack installed with 6-ft. patch cord	Black Brushed Stainless Steel	3.7"L x 3.7"W x 2.93"H	WSBA11BK WSBA11BSS
Two (2) pre-wired 15A outlets with 9-ft. power supply cord (power only)	Black Brushed Stainless Steel	3.7"L x 3.7"W x 2.93"H	WSBA2BK WSBA2BSS

#### **Under Table Mount**

Description	Finish	Dimensions	Catalog Number
Two (2) pre-wired 15A outlets with 9-ft. power supply cord; One (1) Low Voltage Plate included with 1-Unit	Black	6.50"L x 1.75"W x 2.25"H	WSBD21UBK
opening for Hubbell iSTATION modules			

### Work Surface Mount

Description	Finish	Dimensions	Catalog Number	
One (1) pre-wired 15A outlet with 9-ft. power supply co One (1) Hubbell Keystone opening	d;Black Silver	3.57"L x 2.19"W x 2.50"H	WSBE11BK WSBE11SV	
Two (2) pre-wired 15A outlets with 9-ft. power supply cord; Two (2) Hubbell Keystone openings	Black Silver	6.32"L x 2.19"W x 2.50"H	WSBE22BK WSBE22SV	WSBD21UBK
Three (3) pre-wired 15A outlets with 9-ft. power supply cord; One (1) Low Voltage Plate included with 1-Unit opening for Hubbell iSTATION modules	Black Silver	8.25"L x 2.19"W x 2.50"H	WSBE31UBK WSBE31USV	
Mounting bracket with thumb screw (optional)	Black	n/a	WSBECLAMP	_

#### **Recessed Concealed Services**

Description	Finish	Dimensions	Catalog Number
cord; One (1) Low Voltage Plate included with 1-Unit opening for Hubbell iSTATION modules; Two (2)	Black Brushed Anod. Alum. Brushed Stainless Steel	8.98"L x 5.47"W x 2.97"H	WSBB23UBK WSBB23UBAL WSBB23UBSS
cord; Two (2) 1-Unit opening for Hubbell iSTATION modules provided in base of unit	Black Brushed Anod. Alum. Brushed Stainless Steel	8.98"L x 5.47"W x 2.97"H	WSBB43UBK WSBB43UBAL WSBB43UBSS
Empty Enclosure with one (1) duplex opening, One (1) Low Voltage Plate included with 1-Unit opening for Hubbell ISTATION modules; Two (2) additional 1-Unit openings provided in base of unit; intended for field wiring	Black	8.98"L x 5.47"W x 2.97"H	WSBBHWBK

WSBB23UBK



WSBUSB2X2BLK



WSBC21UBK





Architectural finishes for high end spaces. Conceal services while providing an easy interface for users. Cable management features reduce clutter.



ŰL

(ŲĽ

(SP

Catalog Number

**WSBHTRBK** 

**WSBHTRBSS** 

Dimensions

5.25" Diameter

5.25" Diameter

8.90"L x 8.90"W x 13.9"H WSBH42U\*

#### **Grommet Style**

Description	Finish
Two (2) pre-wired 15A outlets with 6-ft. power supply cord; Two (2) Hubbell Keystone openings.	Black Silver
Flush Grommet Cover with dust shield.	Black Silver Brushed Alumi

Black 5.6 Silver Brushed Aluminum Brushed Stainless Steel





WSBF22BK



WSBFGROMSV









WSBFGROMBSS

# Pre-Wired Work Surface Elite Series

### **Recessed Concealed Services**

Description	Finish	Dimensions	Catalog Number
Four (4) pre-wired 15A outlets with 6-ft.	Black	15.0"L x 9.0"W x 6.25"H	WSBG43UBK
power supply cord; Three (3) Low Voltage	Silver		WSBG43USV
Plates included with 1-Unit opening for	Clear Anodized		WSBG43UBAL
Hubbell iSTATION modules	Black Anodized		WSBG43UBBA

Finish

Black

Steel

**Brushed Stainless** 



WSBG43USV (cover doors shown open)

WSBH42U with WSBHTRBK

Note: \*WSBH42U is CSA Certified only.

Trim Ring and Decorative Round Top

Base Unit with Four (4) pre-wired 15A

outlets with 6-ft. power supply cord; Two (2) Low Voltage plates included with 1-Unit opening for Hubbell iSTATION modules Trim Ring and Decorative Round Top

Pop-Up Style\*

Description

### **Replacement Low Voltage Data Plates**

Description	Finish	Dimensions	Catalog Number
Non-metallic low voltage plate, blank	Black	3.18"L x 1.88"W	WSBPLATE1
Non-metallic low voltage plate, 1-Unit Hubbell iSTATION cut-out	Black	3.18"L x 1.88"W	WSBPLATE2

Note: \*For use with WSBEx, WSBBx, WSBGx and WSBHx series.







WSBPLATE2

Integrates with Hubbell keystone devices and Hubbell iSTATION modules for AV and Multi-media solutions.



Square I	Flush Mo	ount Boxes with Cover		SP.
Description		Dimensions	Black	Stainless Steel
2-Gang		6.5"L x 6.5"W x 3.75"H	HBLSHA2	HBLSHA2BSS
Rectang	ular Flus	sh Mount Boxes with Cove	r	
Description		Dimensions	Black	Stainless Steel
2-Gang		10.75"L x 4.06"W x 3.5"H	HBLPHA2	HBLPHA2BSS
4-Gang		10.75"L x 6.5"W x 3.5"H	HBLPHA4	HBLPHA4BSS
Surface	Mount E	Boxes		
Description	Finish	Dimensions	Catalog Number	
2-Gang	Black	4.19"L x 4.81"W x 2.44"H	HBLCON2	
3-Gang	Black	6.19"L x 4.81"W x 2.44"H	HBLCON3	
Recesse	ed Moun	t Boxes		
Description	Finish	Dimensions	Catalog Number	
2-Gang	Black	10.25"L x 7.0"W x 5.88"H	HBLMIR2	
4-Gang	Black	31.0"L x 10.25"W x 5.88"H	HBLMIR4	
Under D	esk Mou	int Boxes		
Description	Finish	Dimensions	Catalog Number	
2-Gang	Black	9.19"L x 3.0"W x 2.88"H	HBLMAR2	
3-Gang	Black	13.69"L x 3.0"W x 2.88"H	HBLMAR3	

# Table Top Boxes

### Low Voltage Only

2.19" Diameter			
Description	Black Anod. Alum.	Clear Anod. Alum	Solid Brass
2 inch diameter hole (1) keystone opening; Keystone modules sold separately	TTBKSBK	TTBKSAL	TTBKSBR
Table Top box; 2 inch diameter hole; (1) XLR microphone jack installed	TTBXLRBK	TTBXLRAL	TTBXLRBR
Pre-Wired Dual-Service 3.88" Diameter			
Description	Black Anod. Alum.	Clear Anod. Alum	Solid Brass
<ul> <li>3.5 inch diameter hole; (1) pre-wired</li> <li>15A outlet with 9 foot power supply cord;</li> <li>(1) 3.5mm screw terminal audio jack;</li> <li>(1) 15-pin gender changer F/F; (2) keystone openings; Keystone modules sold separately</li> </ul>	TTBDS1BK	TTBDS1AL	TTBDS1BR
<ul> <li>3.5 inch diameter hole; (2) pre-wired</li> <li>15A outlets with 9 foot power supply cord;</li> <li>(2) keystone openings; Keystone modules sold separately</li> </ul>	TTBDS2BK	TTBDS2AL	TTBDS2BR



HBLSHA2



HBLPHA2



HBLCON2







TTBXLRBK

TTBKSBK



TTBDS1BK

TTBDS2BK



# **HUBBELL Delivers More.**



Car

Dealership

## **Delivery eTour**

Show Room


This interactive, virtual tour of a city takes visitors through various commercial settings. As users navigate their way through the virtual city, the eTour demonstrates where and how Hubbell Delivery Systems products can be deployed in the floor, through the floor, on the wall, on the surface and from floor to ceiling and demonstrates solutions in these spaces.

Visit www.hubbell-wiring.com to take the tour.



### BIM Models

Visit www.hubbell-wiring.com or seek.autodesk.com to download all Hubbell Wiring device BIM Models.



**Product Page** 

# Customer and Technical Drawings

Customer and technical drawings and installation instructions can be downloaded at www.hubbell-wiring.com.

# Available Literature


Hubbell offers an extensive literature library for product support. Downloadable PDFs are available on line.



Hubbell Wiring Device-Kellems Catalog



Hubbell Delivery Guide



SystemOne Recessed Floor Boxes



SystemOne Recessed Fire-Rated Poke-Throughs



www.hubbell-wiring.com

