

Wire Basket Tray

- T-weld edge on top wire protects both the installer and cable from sharp points
- Flexible, field-adaptable system
- 5mm diameter wire provides outstanding load capacity
- 100% domestic recycled steel
- Buy American Compliant/ U.S. Government Procurement-Eligible

FEATURES

Pre-galvanized steel finish

- Clean attractive finish
- No post-production chemical cleaning and plating
- Free from oils, solvents, and soot from welding operation
- Smooth wire surface free of zinc whiskers
- Cleaned after fabrication to remove soot, manufacturing residue, oils, and metallic particles

Other standard finishes:

- Black powder coat paint
- Pewter powder coat paint
- Stainless steel type 304 and 316
- Electro-zinc plating

Custom color paint and electro-zinc finishes are available.


SPECIFICATIONS

Shaped (flat) cross wire design

- Ideal for CAT6A cabling
- Flat shaped profile reduces stress points that may degrade performance
- Unique design (patent pending)
- Uses the same hardware and supports used for round wire tray

STANDARDS/LISTINGS/VERIFICATIONS

- UL Classified and cUL Classified as equipment grounding conductor



Round Style **Shaped/Flat Style**

Cross sectional view of cross wires.


Shaped cross wires have more surface area and significantly reduces pressure and strain on cables.

Hubbell's wire basket cable tray systems provide superior cable management and protection for electrical power or data communications cabling. Hubbell's wire basket tray system is also field adaptable and is easily installed overhead, on walls, or under floors using various available brackets and supports. Layouts, installations, and changes are quickly and easily configured to requirements with wire cutting tools. Basket tray installs faster than conduit systems and offers more flexibility and capacity.

APPLICATIONS

- Commercial Buildings
- Healthcare Facilities
- Schools/Universities
- Data Centers
- Laboratories
- Manufacturing Facilities

ORDERING INFORMATION



Pre-Galvanized Wire Basket Trays

Height In. (mm)	Width In. (mm)	Length Inches (mm)	Round Wire Tray Catalog No.	Flat Style Wire Tray Catalog No.
2" (51)	4" (102)	118" (3000)	HBT0204	HBT0204S
2" (51)	6" (152)	118" (3000)	HBT0206	HBT0206S
2" (51)	8" (203)	118" (3000)	HBT0208	HBT0208S
2" (51)	12" (305)	118" (3000)	HBT0212	HBT0212S
2" (51)	16" (406)	118" (3000)	HBT0216	HBT0216S
2" (51)	18" (457)	118" (3000)	HBT0218	HBT0218S
2" (51)	20" (508)	118" (3000)	HBT0220	HBT0220S
2" (51)	22" (559)	118" (3000)	HBT0222	HBT0222S
2" (51)	24" (610)	118" (3000)	HBT0224	HBT0224S
2" (51)	26" (660)	118" (3000)	HBT0226	HBT0226S
2" (51)	28" (711)	118" (3000)	HBT0228	HBT0228S
2" (51)	30" (762)	118" (3000)	HBT0230	HBT0230S
2" (51)	32" (813)	118" (3000)	HBT0232	HBT0232S
4" (102)	4" (102)	118" (3000)	HBT0404	HBT0404S
4" (102)	6" (152)	118" (3000)	HBT0406	HBT0406S
4" (102)	8" (203)	118" (3000)	HBT0408	HBT0408S
4" (102)	12" (305)	118" (3000)	HBT0412	HBT0412S
4" (102)	16" (406)	118" (3000)	HBT0416	HBT0416S
4" (102)	18" (457)	118" (3000)	HBT0418	HBT0418S
4" (102)	20" (508)	118" (3000)	HBT0420	HBT0420S
4" (102)	22" (559)	118" (3000)	HBT0422	HBT0422S
4" (102)	24" (610)	118" (3000)	HBT0424	HBT0424S
4" (102)	28" (711)	118" (3000)	HBT0428	HBT0428S
6" (152)	8" (203)	118" (3000)	HBT0608	HBT0608S
6" (152)	12" (305)	118" (3000)	HBT0612	HBT0612S
6" (152)	16" (406)	118" (3000)	HBT0616	HBT0616S
6" (152)	18" (457)	118" (3000)	HBT0618	HBT0618S
6" (152)	20" (508)	118" (3000)	HBT0620	HBT0620S
6" (152)	22" (559)	118" (3000)	HBT0622	HBT0622S
6" (152)	24" (610)	118" (3000)	HBT0624	HBT0624S
8" (203)	8" (203)	118" (3000)	HBT0808	HBT0808S
8" (203)	12" (305)	118" (3000)	HBT0812	HBT0812S
8" (203)	16" (406)	118" (3000)	HBT0816	HBT0816S
8" (203)	18" (457)	118" (3000)	HBT0818	HBT0818S
8" (203)	20" (508)	118" (3000)	HBT0820	HBT0820S

Note: All dimensions are +/- 0.25".

For Black powder coated, add "BK" at the end of the Wire Tray Catalog No.

*Additional colors available.

ACCESSORIES



Supports

Width Inches (mm)	Shelf Support Catalog No.	Center Support Catalog No.	Ceiling Support Catalog No.	Termination Support Catalog No.
4" (102)	HBTSS4	HBTCTRS4	-	-
6" (152)	HBTSS6	HBTCTRS6	-	HBTT6
8" (203)	HBTSS8	HBTCTRS8	-	HBTT8
12" (305)	HBTSS12	HBTCTRS12	HBTCLS12	HBTT12
16" (406)	HBTSS16	HBTCTRS16	HBTCLS16	HBTT16
18" (457)	HBTSS18	HBTCTRS18	HBTCLS18	HBTT18
20" (508)	HBTSS20	HBTCTRS20	HBTCLS20	HBTT20
24" (610)	HBTSS24	HBTCTRS24	HBTCLS24	HBTT24




Brackets

Width Inches (mm)	L Bracket Catalog No.	C Bracket Catalog No.
4" (102)	HBTLB4	HBTCB4
6" (152)	HBTLB6	-
8" (203)	HBTLB8	HBTCB8
12" (305)	HBTLB12	HBTCB12
16" (406)	HBTLB16	-
18" (457)	HBTLB18	HBTCB18
20" (508)	HBTLB20	-
24" (610)	HBTLB24	-

Accessories

Description	Catalog No.
Splice kit (50 pc/box)	HBTSK
Washer support (50 pc/box)	HBTWS
Bar splice (50 pc/box)	HBTBS
Corner splice	HBTC
Trapeze support (50 pc/box)	HBTT
Radius down, 4"	HBTRD4
Radius down, 6"	HBTRD6
Radius down, 12"	HBTRD12
Vertical down	HBTVD
Cable guides	HBTCCG
Rack attachment	HBTRA
Fitting attachment, 2"	HBFA2
Fitting attachment, 4" or 6"	HBFA45
Conduit attachment	HBTA3
Sidcar	HBTS
Electrical box	HBTEB



Note: Tray dividers and bottom inserts are also available.