

# Hubbell SystemOne 6-Inch Recessed Furniture Feed Floor Box

**HUBBELL**<sup>®</sup>  
Wiring Device-Kellems

for Raised Access and Wood Floors

- Installs in 6-inch diameter hole
- Cover features one 2-inch conduit hub for low voltage and one 3/4-inch conduit hub for power
- Available in Six Architectural Finishes
  - Satin nickel plated
  - Antique bronze plated
  - Brushed brass plated
  - Brushed aluminum
  - Black powder coat
  - Gray powder coat
- cULus Listed, Scrub Water Compliant
- Plenum Rated (UL Listed for NEC 300.00(c))



The **AFBS1R6FF** floor box is designed for use in raised access or wood floors. It installs easily into a 6-inch diameter hole and is retained by two pawl arms which swing outwards when tightened with a screw driver. Providing the lowest profile in the industry, the 1/8 inch flange thickness is ADA compliant. The box can also serve as a wiring chamber for power if needed.

Available in six architectural finishes, Hubbell SystemOne Floor Boxes harmonize aesthetics with function and safety.

## FEATURES

- Durable die-cast aluminum cover for higher strength
- One 2-inch knockout on bottom
- One high capacity opening on side for passing low voltage cables through
- One 3/4 and 1/2-inch concentric knockout on side and bottom for power
- Installs in floor tiles or floor with thicknesses of 1 to 2 inches

## APPLICATIONS

Raised access and wood floor applications in commercial and residential buildings.



# Hubbell SystemOne 6-Inch Recessed Furniture Feed Floor Box for Raised Access and Wood Floors

## 6-Inch Recessed Floor Box Ordering Information



Floor Box with temporary installation Cover	<b>AFBS1R6BASE</b>
Floor Box (AFBS1R6BASE) with Brushed Aluminum Finish Cover (AFBS1R6FFCVRALU)	<b>AFBS1R6FFALU</b>
Floor Box (AFBS1R6BASE) with Black Powder Coat Finish Cover (AFBS1R6FFCVRBLK)	<b>AFBS1R6FFBLK</b>
Floor Box (AFBS1R6BASE) with Plated Brushed Brass Finish Cover (AFBS1R6FFCVRBR)	<b>AFBS1R6FFBRS</b>
Floor Box (AFBS1R6BASE) with Plated Antique Bronze Finish Cover (AFBS1R6FFCVRBRZ)	<b>AFBS1R6FFBRZ</b>
Floor Box (AFBS1R6BASE) with Gray Powder Coat Finish Cover (AFBS1R6FFCVRGRY)	<b>AFBS1R6FFGRY</b>
Floor Box (AFBS1R6BASE) with Plated Satin Nickel Finish Cover (AFBS1R6FFCVRNKL)	<b>AFBS1R6FFNKL</b>



AFBS1R6BASE



AFBS1R6FFBLK



AFBS1R6FFBRZ



AFBS1R6DIV



AFBS1R6GROM



AFBS1R6GATE

## Replacement Parts


Low Voltage Divider	<b>AFBS1R6DIV</b>
Low Voltage Grommet	<b>AFBS1R6GROM</b>
Low Voltage Gate	<b>AFBS1R6GATE</b>

## Accessories

2 inch conduit adapter	<b>S1RFFFIT2</b>
------------------------	------------------

## Installation

Hole Diameter	6 inch
Bottom low Voltage Knock out	2 inch
Side low voltage entry	Removable gate, area equal to 2 inch conduit
Bottom Power Knock out	3/4" 1/2" concentric
Side Power knock out	3/4" 1/2" concentric
Fastening	2 pawl arms



## Covers

- Flange is 7.5 inches in diameter
- Flange thickness is 1/8 inches thick and complies with ADA requirements
- Cover load rating is 1000 lbs, for a static load applied through a 3 inch diameter mandrel

## Architectural Cover Finishes

Brushed Aluminum Finish, with 2 inch and 3/4 threaded hubs.



Plated Antique Bronze Finish, With 2 inch and 3/4 threaded hubs.



**AFBS1R6FFCVRALU**

**AFBS1R6FFCVRBRZ**

Plated Brushed Brass Finish, With 2 inch and 3/4 threaded hubs.



Plated Satin Nickel Finish, With 2 inch and 3/4 threaded hubs.



**AFBS1R6FFCVRBRS**

**AFBS1R6FFCVRNKL**

## Powder Coated Cover Finishes

Black Powder Coat Finish, With 2 inch and 3/4 threaded hubs.



**AFBS1R6FFCVRBLK**

Gray Powder Coat Finish, With 2 inch and 3/4 threaded hubs.



**AFBS1R6FFCVRGRY**