

## Outdoor Light Kit with Occupancy Sensor

### *Safe and Secure* *Compact Rugged Design*

The Hubbell Outdoor Light Kit with Occupancy Sensor is an IP65 weatherproof commercial grade unit ideal for single story facilities and residences. It has two super bright LED floodlight heads that produce an even light distribution of nearly 2,000 lumens for a reliable solution for general outdoor lighting applications.

The unit is constructed from corrosion resistant premium powder coated die cast aluminum. It is UL listed for wet locations and is furnished with all necessary hardware for easy mounting in most standard round electrical boxes.

Offered in 3 popular colors this traditional light fixture is 2017 NEC and NEMA 3R compliant. It consumes only 26 watts and lasts over 50,000 hours, providing energy savings and a long product life when compared to compact fluorescent or incandescent light sources. The integrated occupancy sensor has a wide range of coverage of up to 60 feet, and also provides adjustment settings for more precise control.

Either for security, convenience or general illumination, the Hubbell Outdoor Light Kit with Occupancy Sensor is essential for customers' day to day requirements in commercial and residential applications.



- Warm white LED flood lights (3000K) 26 Watt
- Die cast aluminum heads and cover
- Patented multi-directional swivel joint for easy light adjustment
- 180° motion sensor with duration, sensitivity and photocell controls
- Zero arc point switching for longevity
- 2 additional 1/2" threaded openings with closure plug

# Outdoor Light Kit with Occupancy Sensor



**HUBBELL**<sup>®</sup>  
Wiring Device-Kellems

## Outdoor Light Kit with Occupancy Sensor

Description	Color	Catalog Number
Outdoor Flood Light Kit with Sensor;	Gray	<b>S2FLSGY</b>
IP65 compliant; two LED flood light heads;	White	<b>S2FLSW</b>
2000 lumens; 26 watts	Bronze	<b>S2FLSBZ</b>

## Specifications

Timer time-outs	2 seconds to 1.5 hours	
Passive infrared	Dual element pyrometer and Fresnel lens	
Coverage	180° Motion Field, Detection Range 0-65 ft (0-20 m)	
Operating Voltage	120V AC, 13W per flood light head	
Light Specifications	Light Output	997 lumens per head
	Watts	13.3
	Lumens per Watt (Efficacy)	73.7
	Color Accuracy Color Rendering Index (CRI)	82.6
	Light Color Correlated Color Temperature (CCT)	3000K, Warm White
Material	Life	50,000 hours
	Assembly	Die cast aluminum
	Finish	Premium powder coat
Operating environment	Floodlight Head Lens	Tempered glass
	Operating environment	Outdoor use
Ratings	2017 NEC, IP65 rated, NEMA 3R compliant	
Size and weight	Assembled Size: 8.2" Height x 12.67" Width x 5.45" Depth; Weight: 3.4 lb.	
Mounting	Mounts directly to standard 4" round outdoor rated electrical box. Mounting hardware included.	



**S2FLSGY**



**S2FLSW**



**S2FLSBZ**



**HUBBELL**<sup>®</sup>  
Wiring Device-Kellems

[www.hubbell-wiring.com](http://www.hubbell-wiring.com)

