

Health Screening Power Solutions

*Hubbell delivers power and data solutions
for temporary health screening facilities*



Cable Protection



Temporary Power & Lighting



Ground Fault Circuit Protection



Receptacles, Plugs & Connectors



Health Screening Power Solutions

As America begins to reopen, businesses will want to create health screening stations either outside or inside their facility. Larger facilities may need a drive through screening operation, while smaller facilities may need a pop-up tent, all needing convenience power. If a mobile generator is available it can feed Hubbell Spider® Distribution boxes with cables protected by Hubbell's TredTrak to provide localized convenience power. Others may need OSHA approved GFCI line cords from an existing receptacle, then provide both 125V AC power outlets and USB charging ports at the point of use in those sites. Regardless of the requirement, Hubbell has the products customers need to provide safe reliable connections.

Spider® Temporary Power Distribution Boxes

| Rating | Type | Qty | Receptacle | Rating | Cat No |
|-------------|----------------------|-----|---------------|--------|-------------|
| 50A | Straight Blade | 6 | 20A, 125V | | |
| 120/240V AC | Twist-Lock® | 1 | 30A, 250V | | |
| (Maximum) | Twist-Lock® (Inlet) | 1 | 50A, 125/250V | | TPDS |
| | Twist-Lock® (Outlet) | 1 | 50A, 125/250V | | |
| 50A | Twist-Lock® | 6 | 20A, 125V | | |
| 120/240V AC | Twist-Lock® | 1 | 30A, 250V | | |
| (Maximum) | Twist-Lock® (Inlet) | 1 | 50A, 125/250V | | TPDL |
| | Twist-Lock® (Outlet) | 1 | 50A, 125/250V | | |



UL2930 Healthcare Outlet Assembly (HCOA)

| Description | # of Outlets | Cord Length | 15 Amp |
|---|--------------|-------------|--|
| UL 2930 HCOA with L-N surge protection, white | 6 4 | 6' | HBL6MG6 HBL4MG6 |
| UL 2930 HCOA relocatable power tap (RPT), white | 6 4 | 6' | HBL6MGRPT6 HBL4MGRPT6 |
| | 6 4 | 15' | HBL6MGRPT15 HBL4MGRPT15 |



Temporary Power Cables

| Rating | Cable Type | Length (ft) | Cat No |
|--------------|------------|-------------|---------------|
| 50A 125/250V | 6/3, 8/1 | 50 | TPC50 |
| | | 100 | TPC100 |



Temporary Power Receptacle

| Description | Rating | Cat No |
|---|--------------|-------------|
| Pre-wired wall mount receptacle with 3R enclosure and 2' wire leads | 50A 125/250V | SR50 |



LED Stringer Lights

| Description | Rating | Lumen Output | Cat No |
|------------------|----------|--------------|---------------------|
| 50' light string | 15A 125V | 450* | HBL182S50LED |

*Lumens per fixture.



Edison Straight Blade Light Strings

| Description | Rating | Watts | Cat No |
|-------------------|----------|-------|----------------------|
| 100' light string | 15A 125V | 150 | HBL142SJ100PS |




High Bay LED Light

| Description | Rating | Watts | Lumen Output | Cat No |
|------------------|----------|-------|--------------|-------------------|
| LED w/wire guard | 15A 125V | 60 | 7,200 | HBLLEDHB60 |



TredTrak® Systems

| Description | Color | Cat No |
|-------------|-----------------------------|--|
| 5 channel | Straight End caps (pair) | HBLTRED5B HBLTRED5ECB |



ProTrak™ Systems

| Description | Trak Width | Cat No |
|-------------|---------------------------|---|
| 1 channel | Drop over Hinged cover | PROTRK115Y PROTRK1225Y |



Circuit Guard® Portable GFCI Line Cords

| Description | Cord Length | Manual Set |
|--------------------------------------|------------------|--------------------|
| Portable GFCI line cord, 15A 120V AC | 50' (1524.0 cm) | GFP50C15WM |
| | 100' (3048.0 cm) | GFP100C15WM |



Non-Metallic Surge Protective Strips

| Description | # of Outlets | Cord Length | 15 Amp |
|---|--------------|-------------|-----------------------|
| SPD with two USB ports and 90° angle plug | 4 | 6' | HBL4PS1050USBA |



SpikeShield® UL Type 3 Surge Protective Devices

| Description | # of Outlets | Cord Length | 15 Amp |
|---|--------------|-------------|-------------------|
| Heavy duty metal housing with 2-port USB, hospital grade tamper-resistant receptacles and plug, white | 4 | 6' | HBL6HGUSB6 |



HBL® Extra Heavy Duty Specification Grade Receptacles

| Description | Color | 20A 125V |
|--------------------|----------------|------------------------------------|
| Finder groove face | Ivory White | HBL5362I HBL5362W |



Heavy Duty Commercial Grade GFCI Receptacles

| Description | Color | 20A 125V |
|-------------|--------------|------------------------------------|
| Standard | Red White | GFRST20R GFRST20W |



Portable Outlet Box

| Description | Color | Cat No |
|--|--------|----------------|
| Portable outlet box with (2) duplex plates | Yellow | HBL3000 |
| Outlet box cover, GFCI | Gray | HBL3060 |



Straight Male Gray Nylon Cord Connectors

| NPT Hub Size | Cord Dia. Inches (mm) | Form Size | Color Code | Cat No |
|--------------|-----------------------|-----------|------------|------------------|
| ¾ | .38"-.50" (9.5-12.7) | F3 | Blue | SHC1035CR |
| | .50"-.63" (12.7-15.9) | | Brown | SHC1036CR |
| | .63"-.75" (15.9-19.0) | | Yellow | SHC1037CR |
| 1 | .38"-.50" (9.7-12.7) | F4 | Blue | SHC1039CR |

