



# GasBreaker

## GasBreaker All Steel and Steel to Plastic Model EFVs

Since their introduction, millions of GasBreaker EFVs have been sold (more than 5 times as many valves as all other US competitors combined) and installed worldwide, providing tens of billions of field service hours. Today the GasBreaker Excess Flow Valve is known as "The EFV of Choice."

Our steel and steel to plastic EFVs are available in a variety of fabrications from steel sticks to steel to plastic transitions, with threaded or welded ends. They are now available in 1-1/4" IPS and 2" IPS in 28" long weld x weld lengths. We have sizes ranging from 3/4" IPS to 2" IPS.

Contact GasBreaker for additional pipe schedules.



MODEL DESCRIPTION	SLEEVE SIZE	EFV SERIES	LENGTH (IN)	CATALOG NUMBER
EFV #S14	3/4" IPS SCH. 40, WELD X WELD	1800	18	#40002
EFV #S14	1" IPS SCH. 40, WELD X WELD	2600	18	#40107
EFV #S14	1-1/4" IPS SCH. 40, WELD X WELD	5500	28	#40177
EFV #S14	2" IPS SCH. 40, WELD X WELD	10000	28	#40179
EFV #S11	2" IPS SCH. 40, THREAD X THREAD	10000	14	#40162
EFV #S11	1" IPS SCH. 40, THREAD, X THREAD	700	9	#50110
EFV#S22	1" IPS SCH. 80 GRADE B W/1" IPS SOCK. CPLG. IN/OUT	1100	N/A	#40151
EFV #029	3/4" IPS THREAD X 1/2" CTS CONTINENTAL COMP. ADAPTER	300	N/A	#40036
EFV #S18	3/4" IPS WELD TRANS X 1" CTS .099 PIPE, 2406	1100	N/A	#40119

Series: 300, 400, 700, 1100, 1800, 2600 are available in all pipe sizes Series 5500 is available in 1-1/4" & 2" IPS Series 10000 is available only in 2" IPS



99-8008-00 02/2018

[www.hubbell.com](http://www.hubbell.com)



# GasBreaker



Model S11 Steel pipe nipple threaded both ends  
Series 1000 EFV



Model S14 Steel pipe with weld ends  
Series 5500 EFV



Model S18 Transition fitting steel to plastic  
Series 1100 EFV



Model S22 with coupling on inlet/outlet  
Series 1100 EFV



Model S29 Steel pipe nipple threaded on inlet & compression  
adapter for plastic on outlet  
Series 300 EFV



99-8008-00 02/2018

[www.hubbell.com](http://www.hubbell.com)