



GasBreaker


GasBreaker Model 51 EFV

Since their introduction, millions of GasBreaker EFVs have been sold (more than 5 times as many valves as all other US competitors combined) and installed worldwide, providing tens of billions of field service hours. Today the GasBreaker Excess Flow Valve is known as "The EFV of Choice."

GasBreaker's newest EFV, the Model 51, was developed as a solution for a major LDC in the northeast region. Polyethylene service and EFV installations were being delayed by inspectors strict interpretation of acceptable visual criteria for butt fusion joints. The Model 51 was developed as an alternate method to retain the EFV in the PE pipe. The stainless steel sleeve is crimped over the PE pipe, reducing the inner diameter slightly to prevent the EFV from moving downstream.

Features

- Eliminates a butt fusion joint in the service line
- Does not reduce the service line or EFV capacity
- Alternate to Model 41 universal EFV stick, suitable for all applications
- Sleeve is made from corrosion resistant 304 stainless steel
- PE2708 or PE4710
- Available sizes; ½ CTS, ½ IPS, ¾ IPS, 1 CTS, 1 IPS, 1 ¼ IPS, & 2 IPS



| Size | PE Material | EFV Series Catalog Number | | | | | | | | |
|---------------------------|-------------|---------------------------|---------|---------|---------|---------|---------|---------|---------|---------|
| | | 350 | 550 | 700 | 800 | 1100 | 1800 | 2600 | 5500 | 10000 |
| 1/2" CTS .090 X 12" LG | 2708 | 20379GB | 20380GB | N/A | 20381GB | N/A | N/A | N/A | N/A | N/A |
| | 4710 | 25344GB | 25345GB | N/A | 25346GB | N/A | N/A | N/A | N/A | N/A |
| 1" CTS .101 X 12" LG | 2708 | N/A | N/A | 50238GB | N/A | 20382GB | 20383GB | 20384GB | N/A | N/A |
| | 4710 | N/A | N/A | 50241GB | N/A | 25347GB | 25348GB | 25349GB | N/A | N/A |
| 1/2" IPS DR-9.3 X 12" LG | 2708 | 20385GB | 20386GB | N/A | Inquire | N/A | N/A | N/A | N/A | N/A |
| | 4710 | 25350GB | 25351GB | N/A | Inquire | N/A | N/A | N/A | N/A | N/A |
| 3/4" IPS DR-11 X 12" LG | 2708 | N/A | N/A | 50239GB | N/A | 20387GB | 20388GB | 20389GB | N/A | N/A |
| | 4710 | N/A | N/A | 50242GB | N/A | 25352GB | 25353GB | 25354GB | N/A | N/A |
| 1" IPS DR-11 X 12" LG | 2708 | N/A | N/A | 50240GB | N/A | 20390GB | 20391GB | 20392GB | N/A | N/A |
| | 4710 | N/A | N/A | 50243GB | N/A | 25355GB | 25356GB | 25357GB | N/A | N/A |
| 1 1/4" IPS DR-10 X 16" LG | 2708 | N/A | N/A | Inquire | N/A | Inquire | 20393GB | 20394GB | 20395GB | N/A |
| | 4710 | N/A | N/A | Inquire | N/A | Inquire | 25358GB | 25359GB | 25360GB | N/A |
| 2" IPS DR-11 X 16" LG | 2708 | N/A | N/A | Inquire | N/A | Inquire | Inquire | 20396GB | 20397GB | 20398GB |
| | 4710 | N/A | N/A | Inquire | N/A | Inquire | Inquire | 25361GB | 25362GB | 25363GB |




99-8009-00 03/2018



GasBreaker



Model 51 1/2" CTS .090 Series 550 EFV 12" Length




Model 51 3/4" IPS SDR 11 Series 700 EFV 12" Length



Model 51 1" CTS .101 Series 1800 EFV 12" Length



Model 51 1" IPS SDR-11 Series 2600 EFV 12" Length



Model 51 1-1/4" IPS SDR-10 Series 5500 EFV 16" Length



Model 51 2" IPS SDR-11 Series 10,000 EFV 16" Length



99-8009-00 03/2018

www.hubbell.com • 800-558-1373