



Gas Connectors & Accessories



Gas Risers – Anodeless



- Rigid, Pre-bent
- Flexible
- Commercial/Industrial (up to 8 IPS)
- Service Head Adapter

Residential Meter Set



- Prefabricated Meter Sets
- Cast/Prefabricated Meter Bars
- LYCOSAVER Bypass Valves
- Integrated A-9 Bypass Valves

Gas Risers – Anode



- Factory-assembled Transition Risers
- Field-assembled Risers
- Compression Risers

Commercial & Rotary MSAs



Transition Fittings



- Steel to PE Transition Fittings
- Beveled, Threaded, Victaulic, or Flanged Ends
- O.D. or I.D. Coating (up to 16 IPS)

Welded Spools



- API 1104 Certified Welds
- Various Configurations up to 12"

Bypass Valve (A9)



- Stand-alone or Incorporated into Meter Set Assembly Design

Excess Flow Valves (EFV)



- Carrier Option: PE Stick, Reducers, Mechanical Fittings, Services Tees and more
- Trip Points: 450 to 1800 SCFH

Mechanical Fittings



- LYCOFIT®
- Con-StabID Seal® Couplings and Tapping Tees for connecting PE pipe up to 2" diameter

Fabricated/Specialty Products



- Riser and MSA Mounting Brackets and Stakes
- Snow Shields/Ice Guards

Polyethylene Ball Valves



- Medium and High Density PE
- Full and Standard Port
- 3/4 IPS through 16 IPS Sizes

Bollards/Guard Rails



- Standard light and medium duty configurations are available as well as customer specified designs

Meter Manifolds



- Multiple Meter Drops Outlets/--
- Drops from 2 to 20

CUSTOMER SERVICE

OK: (800) 558-1373 CA: (800) 535-9255

www.hubbell.com