

Contractor Tool Series CSMD



Announcing the introduction of the Contractor Series 6-Ton Li-Ion battery platform IN-LINE® crimping tool; a first of its kind that combines performance with an economical price point. With its competitive purchase price, this tool is a cost-effective solution:

For customers currently using mechanical MD6 style crimpers and are looking to upgrade

For those smaller to mid-size contractors and utilities without big budgets, and

For larger utilities as a dedicated crimping tool when big projects arise.

The Contractor Series tool maintains the quality and reliability that BURNDY is recognized for and offers better than industry-average crimp speeds. Fixed, scissor-action crimping jaws are available in three standard configurations; each accepting standard "W" and "X" style die sets..

[Click here to view the introductory video on Contractor Tool Series CSMD](#)



Useful Links

Product Information

[Contractor Series – Catalog Cutsheet](#)

[Contractor Series – Flyer](#)

[Contractor Series – Press Release](#)

Markets & Application

Utility

Commercial & Industrial

Energy

Renewable

Features and Benefits

True one-handed operation for advance, retract and hold functions

Enables the user to easily hold the tool in one hand and focus on the connection with the other

Over-molded Handle

Provides comfort and improved grip, with or without gloves

Audible pressure "pop-off"

Indicates properly completed crimp

350° rotatable head

Allows for maximum flexibility in confined or overhead work areas

Fixed crimping jaw head

Allows for use as a dedicated crimping tool

Safety trigger lock

Provides protection against accidental tool activation

Position is held when the trigger is released

Allows the operator to check alignment prior to crimping

It is powered by Makita 18V battery technology

The tool is offered with a 1-year limited warranty and a 3.0Ah battery and charger are supplied with it.