

# PATCUT1500

## PATRIOT® Battery Actuated Cable Cutter for Copper & Aluminum Mechanically Driven, 18V Lithium-ion

- Variable speed trigger
- Forward/reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- Large, new cutting blade design
- Includes 1 battery, charger and case
- **EP Enhanced Power** tools accept 2.0, 3.0, 4.0, 5.0, and 6.0Ah BL Series Makita batteries

### For Use On:

Aluminum:	up to 1500 kcmil
Copper Flex:	up to 1250 kcmil
Copper (soft drawn):	up to 1000 kcmil
Copper (hard drawn):	up to 750 kcmil

**Do Not Cut Steel or ACSR**

### Variations:

PATCUT1500LI	with 3.0Ah Li-Ion battery
PATCUT1500L5	with 5.0Ah Li-Ion battery
PATCUT1500LCB	tool, no charger or battery



Stainless Steel  
Tooth Guard



LED Worklight



Stabilizing Bumper



### Specifications:

Tool Weight:	8.1 lbs with battery
Size:	15.5" x 6.0" x 4.38"
Operating Voltage:	18 V-DC Lithium-Ion
Recharge Time:	
3.0Ah	30 minutes
5.0Ah	45 minutes
Warranty:	3 year limited warranty (excluding blades) 3 years on battery and charger

### Accessories:

BAT18VLI:	Hi-capacity LI Makita battery (3.0Ah)
BAT18V5AHLI:	Hi-capacity LI Makita battery (5.0Ah)
PATCHGRLI:	120V-AC Makita charger
PATCHGRLLDC:	12/24V-DC Makita charger
CASEPATCUT1500:	Polymer carrying case
PT208620:	Lanyard