


# NEW PATRIOT® PATCUT954HS

*Long Reach, Live Line, Hydraulic Cable Cutter*

## Features & Benefits



- **Industry Exclusive – Only offered by BURNDY® Tools**
- ASTM F711 Rated Pole for live line use
- Battery operated hydraulics for fast cutting time (<15 seconds); less exposure, increased safety when hot sticking
- Rapid Advance Ram
- Large Cut Range – Up to 954 ACSR
- C-Style Head – Easily latch on to lines
- Pistol grip and adjustable assist handle for increased control
- Maximum operating pressure of 10,000 PSI
- Available in two lengths: 82” and 94”
- Hydraulic hoses and fittings comply with SAE requirements
- Accepts multi-Ah Makita lithium-ion batteries ranging from 2.0Ah to 6.0Ah. Offered with either 3.0Ah or 5.0Ah batteries
- 5-year Limited Warranty on Tool (excludes blades and pole itself)
- 3-year Limited Warranty on batteries and charger
- Lifetime Warranty on INFINITY DRIVE® Transmission

Customer Service 1-800-346-4175 | Tool Service Center 1-800-426-8720 | Technical Services 1-800-451-4956 | [www.burndy.com](http://www.burndy.com)



Connecting Power to Your World®

