

Battery Crimper
6 Ton, Scissor Action

PATRIOT® 6 Ton, Scissor Action
 Hydraulic Self-Contained, 18V Lithium-Ion

Tool Series: PATMD-LW

- Light weight, compact and ergonomic design
- Interchangeable scissor action crimping and cutting jaws
- Safety trigger lock and locking jaw tabs
- LED Worklight
- **EP Enhanced Power** — tools accept 2.0, 3.0, 4.0, 5.0, and 6.0Ah Makita batteries

Crimp Capacity		
Connector Type	Conductor Type	Range
Terminals & Splices	Copper	#8 AWG - 500 kcmil
Terminals & Splices	Flex Copper	#8 AWG - 350 kcmil
Terminals & Splices	Aluminum (AAC)	#8 AWG - 350 kcmil
Full-Tension	ACSR	#10 - 4/0 AWG
Taps	Copper	#10 - 2/0 AWG
Taps	AAC or ACSR	#14 - 4/0 AWG
Stirrups	ACSR	#6 - 4/0 AWG

Variations:

- PATMD6LW:** BG and D3 grooves, 3.0Ah batteries, AC charger
PATMD68LW: O and D3 grooves, 3.0Ah batteries, AC charger
PATMD66LW: D3 groove only, 3.0Ah batteries, AC charger
PATMD70003A1: XPJ grooves, 3.0Ah batteries, AC charger
- PATMD6LW5:** BG and D3 grooves, 5.0Ah batteries, AC charger
PATMD68LW5: O and D3 grooves, 5.0Ah batteries, AC charger
PATMD66LW5: D3 groove only, 5.0Ah batteries, AC charger
PATMD70005A1: XPJ grooves, 5.0Ah batteries, AC charger

Standard Crimp/Cut Kits are available supplied with both crimping and cutting jaws. (See separate pages in Cutters Section.)

Customize a tool kit with up to 3 jaws and optional accessories. Contact Customer Service at 1-800-346-4175.

Interchangeable Jaw Assemblies:

- PATMD6LWJAW** Crimp jaw with BG and D3 grooves
PATMD68LWJAW Crimp jaw with O and D3 grooves
PATMD66LWJAW Crimp jaw with D3 groove only
PATMDXPJLWJAW Crimp jaw with X, P, & J grooves
PATMDCUTLWJAW Cutting jaw with ACSR blades
PATMDCUTCLWJAW Cutting jaw with CU/AL blades
PATMDCUTGLWJAW Cutting jaw with GUY blades



Interchangeable Jaws



Specifications:

- Output Force:** 6 Tons
Tool Weight: 6.7 lbs
Length:
 PATMD6LW 18.73"
 PATMD68LW 18.73"
 PATMD66LW 17.85"
 PATMD70003A1 18.40"
Die Style: W and X (with crimping jaws; excluding XPJ, has NICOPRESS® style permanent grooves)
Operating Voltage: 18 V-DC Lithium-Ion
Recharge Time:
 3.0Ah 30 minutes
 5.0Ah 45 minutes
Warranty: 5 year limited warranty
 Lifetime warranty on INFINITY DRIVE®
 3 years on batteries and charger

Accessories:

- BAT18VLI:** Hi-capacity LI Makita battery (3.0Ah)
BAT18V5AHLI: Hi-capacity LI Makita battery (5.0Ah)
PATCHGRLI: 120V-AC Makita charger
PATCHGRLIDC: 12/24V-DC Makita charger
W28K: Cutter Dies (cuts 4-4/0 CU, AL, ACSR)
WDIETREE: W-die holder for 6 die sets
CASEWDIES: W-die case holder for 12 die sets
TOOLBAGMDLI: Tool bag (included with tool)