

Wiley Edge Clip with Cable Tie (ACC-ECT)


High-quality wire management solutions

The WILEY ACC-ECT is the perfect solution to route cable bundles without the need for mounting holes or additional hardware. The ACC-ECT is a nylon-encased plated steel clip that installs onto the module frame flange and allows a cable tie to be routed in both landscape (on the horizontal/perpendicular portion of the module frame) and portrait (on the vertical/parallel portion of the module frame) orientations. The ACC-ECT is available in UV resistant, high impact heat stabilized nylon 6/6 and nylon 12 material; both the 6/6 and 12 have a tensile strength of 50 lb. Nylon 12 makes the ACC-ECT especially suitable in high moisture, corrosive environments or where low temperatures are a factor.

Features and Benefits:

- Route cable bundles without the need for mounting holes or additional hardware
- Installs in a vertical/parallel (90°) or horizontal/perpendicular (180°) orientation
- Steel lances securely anchor clips to module frames or purlins
- Offered in various nylon types with 50 lb tensile strength:
 - UV resistant, high impact heat stabilized Nylon 6/6
 - UV resistant Nylon 12 which provides excellent UV, chemical and moisture resistance

Style B - Horizontal/Perpendicular Installation



Style A - Vertical/Parallel Installation



Style B - Horizontal/Perpendicular Installation

Style A - Vertical/Parallel Installation

Part Key

Family	ACC	Acme Cable Clip
Type	ECT	Edge Clip Tie
Style	A	Vertical/Parallel (90°) Installation
	B	Horizontal/Perpendicular (180°) Installation

Catalog Number	Style	Nylon Type	Cable Tie Length	Max. Bundle Dia.
ACC-ECTA68	A	6/6	8" / 200mm	1.95" / 49.5mm
ACC-ECTA611			11" / 280mm	2.95" / 74.8mm
ACC-ECTA614			14" / 360mm	3.94" / 100mm
ACC-ECTA128		12	8" / 200mm	1.95" / 49.5mm
ACC-ECTA1211			11" / 280mm	2.95" / 74.8mm
ACC-ECTA1214			14" / 360mm	3.94" / 100mm
ACC-ECTB68	B	6/6	8" / 200mm	1.95" / 49.5mm
ACC-ECTB611			11" / 280mm	2.95" / 74.8mm
ACC-ECTB614			14" / 360mm	3.94" / 100mm
ACC-ECTB128		12	8" / 200mm	1.95" / 49.5mm
ACC-ECTB1211			11" / 280mm	2.95" / 74.8mm
ACC-ECTB1214			14" / 360mm	3.94" / 100mm

Edge Clip Compartment

