

BURNDY® TOOLS

PATRIOT® PAT750
12-TON C-HEAD
SERIES



Connecting Power to Your World®



BURNDY® PATRIOT® PAT750 SERIES

FEATURES & BENEFITS



TRUST THE BURNDY® ENGINEERED SYSTEM

MODELS, SPECIFICATIONS & CAPACITIES

MODELS	
PAT750LI	Tool, 3Ah, 120V AC
PAT750L5	Tool, 5Ah, 120V AC
PAT750LCB	Tool, No Charger/Batteries

SPECIFICATIONS	
Output Force	12 Tons
Tool Weight	15.7 lbs
Size	15.75" x 13.5" x 3.5"
Die Style	U Style
Operating Voltage	18 V-DC Lithium-ion
Recharge Time	30 minutes (3.0Ah)
	45 minutes (5.0Ah)
Warranty	5 year limited warranty
	Lifetime warranty on INFINITY DRIVE®
	3 years on batteries and charger



CRIMPING CAPACITIES	TERMINALS & SPLICES	TENSION SLEEVES	TAPS	AERIAL CABLE	HYGROUND®
Copper	#8 AWG - 750 kcmil	#8 Solid - 500 kcmil	#14 Solid - 500 kcmil	#6 AWG - 500 kcmil	#8 AWG - 500 kcmil
Aluminum	#8 AWG - 750 kcmil	#8 Solid - 587.2 kcmil	#8 AWG - 500 kcmil		
ACSR	#4 - 556.5 kcmil	#4 - 556.5 kcmil			
Ground Rod					1/2" - 1" Diameter

**WHEN FACING THE UNPREDICTABLE,
YOU'RE NOT ALONE...**

 BURNDY HAS YOUR BACK!

**PROFESSIONAL GRADE
TOOLS YOU KNOW
TOOLS YOU TRUST**



Customer Service Department
7 Aviation Park Drive
Londonderry, NH 03053
1-800-346-4175
1-800-451-4956 (Technical Services)
1-603-647-5299 (International)

Canada
1-800-361-6975 (Quebec)
1-800-387-6487 (All other provinces)

Mexico
011-52-722-265-4400

Brazil
011-55-11-5515-7225

Tool Service Center
Littleton Industrial Park
Littleton, NH 03561
1-800-426-8720

www.burndy.com | 1-800-346-4175

 BURNDY

Connecting Power to Your World®

